




0	Creation	BLONDEL N.	11.05.2006	DP 11.05.2006
Ind.	Object	Drawn :	Date :	Checked : Date :
TYPE J LEAF E06010		N° 621-2237		
		Material :	Scale :	
		-	N.T.S	
		unless otherwise specified Generale tolerances ± 0.1 mm		
		94-05-08-TE-079 Rév.2		



4	Heat shrink	PE
3	Sleeve	PE
2	cable	FG/S.SBraid
1	Leaf	AISI 304L
<b>Tag</b>	<b>Description</b>	<b>Material</b>


0	Creation	BLONDEL N.	11.05.2006	DP	11.05.2006
Ind.	Object	Drawn :	Date :	Checked :	Date :

TYPE J LEAF E06010	<b>N° 621-2237</b>
-----------------------	--------------------

	Material : -	Scale : <b>N.T.S</b>
	<small>unless otherwise specified Generale tolerance: ± 0.1 mm</small>	

**Description**

Type J Leaf

**Thermocouple type**

J

**Grounded or Ungrounded**

Grounded

According to IEC-BS 4937 60584-2 & IEC-BS 4937 60584-3

**RoHS compliance**

Yes

**Accuracy Class 2**

±2.5°C or ±0.0075xT

**Colour Codes IEC 60584**

+VE arm	black
-VE arm	white
overall	black

**Temperature**

Range	-50 to +750° C
Operating	-50 to +400° C

**Cable characteristics**

	7x0.2
Section	0.22 mm <sup>2</sup>
Conductor Insulation	Glass fiber
Braid	StainlessSteel
Length	2000 mm

**Leaf dimensions**



25 x 13x 0.15

**Connection**

On side of the leaf

**Application**

contact temperature

0	Creation	BLONDEL N.	11.05.06	DP	11.05.06
Ind.	Object	Drawn :	Date :	Checked :	Date :
<b>TYPE J LEAF E06010</b>			<b>N° 621-2237</b>		
			Material :		Scale :
					N.T.S
			Unless otherwise specified generales tolerances ± 0,1mm		 <small>94-05-08-TE-079 Rév.2</small>