

Professionally approved products.

## Datasheet

# Aluminium Electrolytic Capacitor

RS Stock number 711-1179



### Specifications:


Item	Performance Characteristics																																												
Operating Temperature Range	-40 to +105°C	-25 to +105°C																																											
Rated Voltage Range	6.3 to 100 VDC	160 to 450 VDC																																											
Capacitance Tolerance	± 20% (120Hz, +20°C)																																												
Leakage Current (at 20°C, max.)	I < 0.01 CV or 3 (µA). After 1 minute whichever is greater measured with rated working voltage applied.	I < 0.03 CV or 3 (µA). After 1 minute with rated working voltage applied.																																											
Dissipation Factor (120Hz, 20°C)	<table border="1"> <thead> <tr> <th>Working voltage (VDC)</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> <th>63</th> <th>100</th> <th>160</th> <th>200</th> <th>250</th> <th>350</th> <th>400</th> <th>450</th> </tr> </thead> <tbody> <tr> <td>D.F (%) Max.</td> <td>23</td> <td>20</td> <td>16</td> <td>14</td> <td>12</td> <td>10</td> <td>10</td> <td>10</td> <td>15</td> <td>15</td> <td>16</td> <td>20</td> <td>20</td> <td>20</td> </tr> </tbody> </table>															Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20
	Working voltage (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																														
D.F (%) Max.	23	20	16	14	12	10	10	10	15	15	16	20	20	20																															
For capacitance > 1000µ F, add 2% per another 1000µ (+20°C at 120Hz)																																													

# Professionally approved products. Datasheet

## Specifications:

Item	Performance Characteristics																																													
Low Temperature Characteristics (at 120Hz)	Impedance ratio max.																																													
	<table border="1"> <thead> <tr> <th>W.V (VDC)</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> <th>63</th> <th>100</th> <th>160</th> <th>200</th> <th>250</th> <th>350</th> <th>400</th> <th>450</th> </tr> </thead> <tbody> <tr> <td>Z-25°C/+20°C</td> <td>4</td> <td>3</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>3</td> <td>3</td> <td>3</td> <td>5</td> <td>6</td> <td>15</td> </tr> <tr> <td>Z-40°C/+20°C</td> <td>9</td> <td>6</td> <td>4</td> <td>4</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> <td>-</td> </tr> </tbody> </table>	W.V (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	Z-25°C/+20°C	4	3	2	2	2	2	2	2	3	3	3	5	6	15	Z-40°C/+20°C	9	6	4	4	3	3	3	3	-	-	-	-	-	-
	W.V (VDC)	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																															
Z-25°C/+20°C	4	3	2	2	2	2	2	2	3	3	3	5	6	15																																
Z-40°C/+20°C	9	6	4	4	3	3	3	3	-	-	-	-	-	-																																
For capacitance value 1000µF, add 0.5 per another 1000µF for -25°C/+20°C For capacitance value 1000µF, add 1 per another 1000µF for -40°C/+20°C																																														
Load Life	Test Conditions: Duration time: 2000hrs Ambient temperature: +105°C Applied voltage: Rated DC working voltage After test requirements: +20°C After test requirements: $\leq \pm 20\%$ of initial measured value Dissipation Factor: $\leq 200\%$ of the initial specified value Leakage Current: $\leq$ the initial specified value																																													
Shelf Life	Test Conditions: Duration time: 1000hrs Ambient temperature: +105°C Applied Voltage: None After test requirements at +20°C: Same limits as load life. Pre-treatment for measurements shall be conducted after application of DC working voltage for 30 minutes.																																													

## Diagram of Dimensions:



(Unit: mm)

D	5	6	8	10	13	16	18	22	25
F	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	12
$\phi d$	0.5		0.6			0.8		1.0	

## Professionally approved products. Datasheet

### Features:

- Used in communication equipment's, switching power supply, etc.
- Safety vent construction design

### Ripple Current & Temperature

Temperature (°C)	45	60	70	85	105
Multiplier	2.10	1.90	1.65	1.40	1.00

### Ripple Current & Frequency Multipliers

CAP (μF)/Hz	50 (60)	120	400	1K	10K	50 – 100K
$CAP \leq 10$	0.8	1.0	1.30	1.45	1.65	1.70
$10 < CAP \leq 100$	0.8	1.0	1.23	1.36	1.48	1.53
$100 < CAP \leq 1000$	0.8	1.0	1.16	1.25	1.35	1.38
$1000 < CAP$	0.8	1.0	1.11	1.18	1.25	1.28

# Professionally approved products.

## Datasheet

Case Size

 $\varnothing$  D x L (mm)

uF	6.3		{8}		10		{13}		16		{20}		25		{32}		35		{44}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
4.7													5x11	27	5x11	29				
6.8													5x11	35	5x11	38				
10										5x11	38	5x11	40	5x11	42					
22					5x11	50	5x11	56	5x11	56	5x11	60	5x11	62						
33	5x11	56	5x11	60	5x11	65	5x11	70	5x11	78	5x11	82	5x11	88	5x11	98	5x11	110	115	
47	5x11	68	5x11	72	5x11	100	5x11	105	5x11	105	6.3x11	120	5x11	140	5x11	140	6.3x11	140		
68	5x11	77	5x11	82	5x11	105	5x11	115	5x11	115	6.3x11	135	5x11	165	5x11	165	6.3x11	165	180	
100	5x11	98	5x11	110	5x11	135	5x11	150	5x11	150	6.3x11	180	5x11	180	5x11	180	6.3x11	180	300	
220	5x11 6.3x11	160 180	6.3x11	180	6.3x11	220	6.3x11 8x11	240	6.3x11	240	8x11	300	8x11	330	8x11	330	8x11	330	410	
330	6.3x11	200	6.3x11 8x11	260 280	6.3x11	300	8x11	350	6.3x11	350	8x11 10x12	410	8x11	420	8x11	420	8x11	420	480	
470	6.3x11 8x11	280 310	6.3x11 8x11	300 315	6.3x11	380	8x11 10x12	445	6.3x11	445	8x14 10x12 10x20	520	8x14	520	8x14	520	8x14	520	520	
560	8x11	320	8x11	330	8x11	410	10x12	460	8x11	460	10x15	540	8x11	540	8x11	540	8x11	540	540	
680	8x11	360	10x12	420	10x12	480	10x12	520	10x12	520	10x15	650	10x12	650	10x15	650	10x15	650	650	
820	8x11	390	10x12	480	10x12	550	10x15	640	10x12	640	10x15	760	10x12	760	10x15	760	10x15	760	760	
1000	8x11	420	10x12 10x15	530 580	10x12	570	8x16 10x15 10x17	630	10x12	630	10x15	870	10x12	870	10x15	870	10x15	870	870	
1200	10x15	480	10x15	650	10x15	710	10x20	850	10x15	850	10x20	970	10x15	970	10x20	970	10x20	970	970	
1500	10x15	620	10x17	770	10x17	820	10x20	910	10x17	910	13x21	1300	10x17	1300	13x21	1300	13x21	1300	1300	
2200	10x17 10x20	780 800	10x17 10x20	870 900	10x17	1020	13x21 13x26	1270	10x17	1270	13x21 13x26 16x16	1400	13x21	1400	13x21	1400	13x21	1400	1400	
2700	10x20	850	13x21	920	13x21	1100	13x21	1330	10x20	1330	16x26	1500	10x20	1500	16x26	1500	16x26	1500	1500	
3300	10x20 13x21	970 1010	10x25 13x21	1110 1160	10x25	1220	13x21 13x26	1540	10x25	1540	16x26 16x31	1680	10x25	1680	16x26	1680	16x26	1680	1680	
4700	10x25 13x21	1160 1200	13x21 13x26	1360 1380	13x21	1620	16x26	1800	13x21	1800	18x36	1900	13x21	1900	18x36	1900	18x36	1900	1900	
5600	13x26	1320	16x26	1510	16x26	1720	16x31	1890	13x26	1890	18x36	2000	13x26	2000	18x36	2000	18x36	2000	2000	
6800	16x26	1470	16x26	1680	16x26	1880	16x31	2040	16x26	2040	18x41	2090	16x26	2090	18x41	2090	18x41	2090	2090	
8200	16x26	1520	16x31	1840	16x31	1950	16x36	2090	16x31	2090	22x42	2180	16x31	2180	22x42	2180	22x42	2180	2180	
10000	16x26 16x31	1690 1740	16x36 18x36	1900 1980	16x36	2080	18x36 18x41	2200	16x36	2200	25x44	2300	16x36	2300	25x44	2300	25x44	2300	2300	
15000	16x36 18x36	2080 2190	18x36	2230	18x36	2300	22x40	2500	18x36	2500	-	-	18x36	-	-	-	-	-	-	

Ripple Current(mA,rms)at105□120Hz

## Professionally approved products. Datasheet

 Case Size Ø D x L (mm)

uF	50 {63}		63 {79}		100 {125}		160 {200}		200 {250}	
	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.1	5x11	1.3	5x11	1.3	5x11	1.3	-	-	-	-
0.22	5x11	2.9	5x11	2.9	5x11	2.9	-	-	-	-
0.33	5x11	4.2	5x11	4.2	5x11	4.2	-	-	-	-
0.47	5x11	8	5x11	8	5x11	8	5x11	12	5x11	12
1	5x11	14	5x11	14	5x11	15	5x11	17	6.3x11	17
2.2	5x11	20	5x11	21	5x11	22	6.3x11	26	6.3x11	33
3.3	5x11	26	5x11	28	5x11	30	6.3x11	32	6.3x11	43
4.7	5x11	32	5x11	34	5x11	36	6.3x11 8x11	36 42	8x11	51
6.8	5x11	40	5x11	42	6.3x11	47	8x11	56	10x12	63
10	5x11	50	5x11	51	6.3x11	60	8x11 10x12	75 78	10x12 10x15	83 90
22	5x11	75	5x11 6.3x11	75 85	6.3x11 8x11	98 105	10x15	105	10x20	135
33	5x11 6.3x11	90 95	6.3x11 8x11	105 115	8x11 10x12	145 155	10x20	170	13x21	180
47	6.3x11	120	6.3x11 8x11	145 155	10x12 10x15	170 180	13x21	210	13x21 13x26	220 230
68	8x11	155	8x11	185	10x15	240	13x26	280	16x26	300
100	8x11	200	10x12	240	10x20	290	13x26 16x26	320 330	16x26	360
220	10x12 10x15	350 380	10x17 10x20	400 430	13x26 16x26	530 560	16x36	580	18x36	590
330	10x17 10x20	450 470	13x21	570	16x26	680	18x31	710	18x36	740
470	13x21	610	13x21 13x26 16x26	640 700 720	16x26 16x31	840 860	18x41	880	22x42	890
560	13x21	660	13x26	770	16x36	880	-	-	-	-
680	13x26	770	16x26	880	16x36	920	-	-	-	-
820	13x26	850	16x26	920	18x31	970	-	-	-	-
1000	13x26 16x26	900 1010	16x32 16x36	1190 1220	18x41	1250	-	-	-	-
1500	16x31	1300	18x31	1350	22x42	1500	-	-	-	-
2200	18x36	1550	18x36	1590	25x44	1880	-	-	-	-
2700	18x36	1610	22x42	1720	-	-	-	-	-	-
3300	18x36	1780	22x42	1900	-	-	-	-	-	-
4700	22x42	2050	25x44	2200	-	-	-	-	-	-
5600	25x42	2160	-	-	-	-	-	-	-	-
6800	25x44	2280	-	-	-	-	-	-	-	-

Ripple Current(mA,rms)at105□120Hz

## Professionally approved products. Datasheet

Case Size		Ø D x L (mm)							
uF	WV {SV}	{300}		{400}		{450}		{500}	
		Size	Ripple	Size	Ripple	Size	Ripple	Size	Ripple
0.47		5x11	12	6.3x11	15	6.3x11	15	6.3x11	15
1		6.3x11	17	6.3x11	20	8x11	22	8x11	22
2.2		8x11	36	10x12	39	10x12	39	10x12	39
3.3		8x11	43	10x12	53	10x12 10x15	53 55	10x15 10x20	53 55
4.7		10x12	51	10x12 10x15	63 66	10x15	69	10x20	64
6.8		10x12	70	10x15	79	10x15	85	10x20	75
10		10x15	90	10x20	110	10x15 10x20 13x21	100 112 115	13x21 13x26	92 98
22		10x20	160	13x26	180	13x21 16x26	170 190	16x26 16x31	175 180
33		13x21 13x26	175 180	16x26	190	16x26	220	16x36	210
47		13x26	240	16x31	250	16x31	300	16x36	280
68		16x26	320	16x31	330	16x36	355	18x36	330
100		16x31	400	18x36	420	18x36	450	-	-
120						18x31	440		

Ripple Current(mA,rms)at105□120Hz