


BFO D22-XA-MB-PAK-10-02 BFO0062



Electrical connection

Cable diameter D	1.00 mm
Cable length	2 m
Cable, note	can be trimmed
Connection	Ø 2.2 mm
Connection type	Adapter sleeve, 2.00 m, PVC

Electrical data

Active surface, fibers	Ø 0.5 mm (2x)
------------------------	---------------

Environmental conditions

Ambient temperature	-40...70 °C
Ambient temperature connection area	Acc. to fiber optic sensor
Protection type IEC 60529	IP65

General data

Basic standard	IEC 60947-5-2
Reference base unit	BFB 75K-001-..
Version	Ø 3, thin point, 90° optics

Material

Active surface, fiber arrangement	Adjacent to one another
Fiber type material	PMMA
Housing material	Stainless steel

Material jacket	PVC
-----------------	-----

Mechanical data

Cable, bending radius min.	25 mm
Dimension	Ø 3 x 35 mm
Fastening detail	Diameter 3.0 mm
Fiber optic cable, structure	Single fiber in plastic jacket
Tensile load max. at 20 °C	6 N (max. 3s)

Optical data

Principle of optical operation	Retroreflective sensor
--------------------------------	------------------------

Range/Distance

Effective operating distance Sr	35 mm
Range	35 mm
Rated operating distance Sn	35 mm

Remarks

The cutting tool is included in the scope of delivery order other accessories separately.
Cut cable to length: use suitable cutting tool. Make a single cut, vertical to cable axis. The cut quality can affect the switching distance.
Reference object (target): gray card, 200 x 200, 90 % remission, axial approach.
Route fiber optic cable so that no excessive tensile, compression or torsional forces are permitted. Observe permissible bending radiuses. Installation may affect the switching distance.

BFO D22-XA-MB-PAK-10-02
BFO0062

Symbols for Optoelectronic Sensors

