

## Professionally approved products.

# Datasheet RS SPDT Thermostat, 0°C +120°C

## **RS Stock number 733-4710**

### <u>Application</u>

Altecnic control thermostats are designed for panel or bracket mounting in a central boiler plant room in a commercial or public building.

They are intended to measure and help control the temperature in calorifiers, hot water cylinders and other similar appliances by measuring the surface temperature or on adjacent pipework. When the switching temperature has been reached the thermostat

breaks the electrical circuit causing a motorised control valve to close and isolate the primary hot water supply to the appliance. When the temperature in the vessel falls below the set temperature less the temperature differential  $\Delta T$  the thermostat switches, closes

the electrical circuit and the motorised control valve opens. The thermostats require four M4 x 6 long screws to mount the thermostat and control knob bezel to the panel or bracket – not supplied. A range of control knobs are available to match the operating range of

thermostats but are not included as part of the thermostat and must be ordered separately.

**Technical Specification** 


Electricity supply: 15(2.5)A / 250V AC


Switching point with thermostat at temperature: 20°C

Marked:Sensing element: liquid filled

Capillary and sensing element material: copper

Product Code	Temp Range °C	ΔT °C	Max Body °C	Max Bulb °C
IM-TR2/540043	-35 to 35 ± 2	1.5 ± 1	80	65
IM-TR2/540030	0 to 40 ± 2	3 ± 1	80	70
IM-TR2/540010	0 to 90 ± 3	4 ± 1	85	150
IM-TR2/540310	0 to 90 ± 3	4 ± 1	85	150
IM-TR2/540160	0 to 120 ± 3	4 ± 1	80	150
IM-TR2/540140	40 to 210 ± 6	9 ±2	85	260
IM-TR2/540020	50 to 300 ±8	10 ± 2	85	330








## Professionally approved products.

## **Datasheet**

# RS SPDT Thermostat, 0°C +120°C

**RS Stock number 733-4710** 



### **Application**

Altecnic control thermostats are designed for panel or bracket mounting in a central boiler plant room in a commercial or public building.

They are intended to measure and help control the temperature in calorifiers, hot water cylinders and other similar appliances by measuring the surface temperature or on adjacent pipework. When the switching temperature has been reached the thermostat breaks the electrical circuit causing a motorised control valve to close and isolate the primary hot water supply to the appliance. When the temperature in the vessel falls below the set temperature less the temperature differential  $\Delta T$  the thermostat switches, closes the electrical circuit and the motorised control valve opens.

The thermostats require four M4 x 6 long screws to mount the thermostat and control knob bezel to the panel or bracket – not supplied. A range of control knobs are available to match the operating range of

thermostats but are not included as part of the thermostat and must be ordered separately.

## **Technical Specification**

Electricity supply: 15(2.5)A / 250V AC

Switching point with thermostat at temperature: 20°C


Marked: Sensing element: Liquid filled

Capillary and sensing element material: Copper



# Professionally approved products.

# **Datasheet**



Product Code	Temp Range °C	ΔT °C	Max Body °C	Max Bulb °C
IM-TR2/540043	-35 to 35 ± 2	1.5 ± 1	80	65
IM-TR2/540030	0 to 40 ± 2	3 ± 1	80	70
IM-TR2/540010	0 to 90 ± 3	4 ± 1	85	150
IM-TR2/540310	0 to 90 ± 3	4 ± 1	85	150
IM-TR2/540160	0 to 120 ± 3	4 ± 1	80	150
IM-TR2/540140	40 to 210 ± 6	9 ±2	85	260
IM-TR2/540020	50 to 300 ±8	10 ± 2	85	330