

Data sheet

MCX Straight Surface Mount Jack

RS stock No: **7385793**

NO	DESCRIPTION	DATE
①	MODIFICATION PARTS ①	03.15.11'
②	MODIFICATION PARTS ①②③ MODIFICATION LAYOUT	07.08.11'

1.0 ELECTRICAL

1.1 FREQUENCY RANGE: DC-8 GHz
 1.2 NOMINAL IMPEDANCE: 50 OHM
 1.3 WORKING VOLTAGE: 335 VOLTS MAX
 1.4 PROOF VOLTAGE: 1000 VOLTS

2.0 MATERIALS

2.1 BODIES: BRASS PER JIS-C3604
 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B190 UNS C17900
 2.3 INSULATION: TETRAF PER ASTM D1487 AND ASTM D1710

3.0 FINISHES AND OTHERS

3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

4.1 INTERFACE IN ACCORDANCE WITH: CECC 22220

5.0 ENVIRONMENTAL

5.1 OPERATING TEMPERATURE RANGE: -55° C TO +155° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
3	BODY	BRASS	1	TIN 120μ" MIN.
2	INSULATION	TRIFLON	1	NONE
1	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 30μ" MIN.

APPROVED

by _____

DATE:

DESCRIPTION		MCX STRAIGHT SURFACE MOUNT JACK RECEPTACLE	
製圖	DRAWN Yoko	TOLERANCE	品名 27-05-3 T.G.T
檢圖	CHECK Jenny	.X ±0.2	TITLE \ROHS COMPLIANT (500)
承認	APPROVAL Jenny	.XX ±0.1	DATE 09.19.97
標準	ANGLE ±5°	.XXX ±0.05	版次 B-2
		單位 mm(In)	DWG.NO. 27-0009
		比例 8:1	

