


Data sheet

N Plug to N Jack Right Angle Adapter

RS stock No: 7581610



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-11 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 1000 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 2500 VOLTS
- 1.5 VSWR: 1.3 MAX.@10 GHz

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3804
- 2.2 CENTER CONTACT: BRASS PER JIS-C3804
- 2.3 INSULATION: TEFLON PER ASTM D1487 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

9	SHELL	BRASS	1	NICKEL 100µ" MIN.
8	CHASSIS II	BRASS	1	NICKEL 100µ" MIN.
7	O-RING	SILICONE	1	RED
6	BODY II	BRASS	1	NICKEL 100µ" MIN.
5	INSULATION II	TEFLON	1	NONE
4	INSULATION I	TEFLON	1	NONE
3	CENTER CONTACT	BRASS	1	GOLD 30µ" MIN.
2	CHASSIS I	BRASS	1	NICKEL 100µ" MIN.
1	BODY I	BRASS	1	NICKEL 100µ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by _____ DATE: _____

DESCRIPTION			N RIGHT ANGLE PLUG-JACK							
製圖	DRAWN	TOLERANCE		品名	64-05	T.G.N	日期	DATE	版次	REV.
	Gina	X	±0.2	TITLE	ROHS COMPLIANT (500)		10.27.11'		A-0	
檢圖	CHECK	XX	±0.1	單位	DWG.NO. 64-0006					
	Arc			mm(in)						
認定	APPROVAL	XXX	±0.05	比例	SCALE					
	Jenny	ANGLE	±5°	3:1						



