

PLUG-IN RELAY COMPLETE UNIT AC 24V, 3 CO  
CONTACT LED MODULE RED STANDARD PLUG-IN  
SOCKET SCREW TERMINAL 3.5 MM PINNING



Figure similar

General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• at AC		
— at 50 Hz Rated value		
— minimum	V	24
— maximum	V	24
— at 60 Hz Rated value		
— minimum	V	24
— maximum	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		3
Operating current of the auxiliary contacts		
• at DC-13		

- at 24 V
- at AC-15
- at 230 V

A	8
A	5
<b>Design of the switching function positively driven</b>	No
<b>Switching behavior</b>	monostable

#### Mechanical data:

<b>Type of electrical connection</b>		screw-type terminals
<b>Design of the relay operating mechanism</b>		poled
<b>Product component Plug-in socket</b>		Yes
<b>Width</b>	mm	28
<b>Height</b>	mm	72
<b>Depth</b>	mm	74

#### Certificates/ approvals:

General Product Approval

Declaration of Conformity



#### Further information

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZS:PT3A5R24>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT3A5R24>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZS:PT3A5R24&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZS:PT3A5R24&lang=en)

last modified:

18.07.2015