



**201-8**

**HEAVY DUTY SPACE THERMOSTATS FOR COOLING**

Designed for Use in Garages, Factories, Warehouses and Similar Commercial and Industrial Installations

**FEATURES**

- Dust, moisture and vermin resistant heavy metal case.
- No leveling required – Mounts in any position.
- Quick response to temperature changes.
- Nickel plated element.
- Extra rugged switch mechanism.

**SPECIFICATIONS**

Dimensions . . . . . 5<sup>3</sup>/<sub>8</sub>" H x 2<sup>1</sup>/<sub>2</sub>" W x 2<sup>5</sup>/<sub>16</sub>" D (Vertical)  
 Finish . . . . . Grey Color  
 Agency . . . . . U.L. listed and C.S.A. approved

Model Number	Range	Differential	System Action	Full Electrical Rating	Bulb Size	Capillary Length	Motor Rating (Full Load)		Resistive (Non-Inductive)	
							120 VAC	240 VAC	120 VAC	240 VAC
201-8	20 to 90°F (-7 to 32°C)	Adj. 3 to 20°F (2 to 11°C)	Close on Rise	FGH See page 222	16.0A	8.0A	5.6A	2.8A	25.0A	22.0A



**179-1**

**LINE VOLTAGE THERMOSTAT FOR HEATING / COOLING**

Control Suitable for Fans or Water Solenoids on Heating / Cooling Convector or Any Similar Application that Requires a Heavy Duty Room Thermostat with Single Pole, Double Throw (SPDT) Switch Action

**FEATURES**

- Can handle many cooling installations without use of relay or motor starter.
- Heavy gauge steel case – Mounts on vertical 2" x 4" box or flus to wall.
- Hydraulic action element – Unaffected by motion – No leveling required.
- Dustproof case.

**SPECIFICATIONS**

Dimensions . . . . . 6" H x 2<sup>3</sup>/<sub>4</sub>" W x 2<sup>1</sup>/<sub>2</sub>" D  
 Finish . . . . . Grey Color  
 Agency . . . . . U.L. listed and C.S.A. approved

**PARTS AND ACCESSORIES** See end of thermostats section for additional parts and accessories

- Thermostat Guards — see pages 34–35

Model Number	Range	Differential	Action	Full Electrical Rating	Motor Rating (Full Load)	
					120 VAC	240 VAC
179-1	55 to 95°F (13 to 35°C)	Fixed 3.0°F (1.6°C)	SPDT (Heat / Cool)	SPDT See page 222	7.4A	3.7