

**Professionally approved products.
Datasheet**

IEC Inlet-C14

RS Stock number 811-7200



Specifications:

Current & Voltage Rating:

10A (VDE), 15A (UL, CSA) 250VAC

Product Description:

IEC inlet with snap mounting, PCB terminals

Panel Thickness:

Standard – 1.5, other – on request

Permissible Temperature – for soldering:

270°C for 5 seconds max.

Permissible Temperature – with/without load:

0 to 70°C

Approvals:

UL(C, US), VDE, CE

Reference Standard:

IEC 60320-1

Material – Body:

Nylon-6, 20% GF, V2

Material – Terminals:

Copper alloy, Tin plating

Terminals:

Solder Type

Mounting:

PCB or Panel, snap in type

HV Breakdown test for 1 minute:

2 KVAC

Insulation Resistance at 500VDC:

1000MΩ min.

Contact Resistance (initial):

10mΩ max.

MOQ:

100 nos.

Professionally approved products. Datasheet

Unit: mm

