

LMT110



LMACE-A12E/QPKG/1/US

1: tightening torque 2025 Nm					
		d FDA Made in Germany			
Product characteristics					
Electronic level sensor					
Connector					
Process connection: G ½ A					
Gold-plated contacts					
Probe length: 11 mm					
2 switching outputs					
Application					
Application		oils, grease			
Recommended media		oils, grease			
Cannot be used for:		water, water-based media			
Medium temperature oil					
- Continuous	[°C]	0100			
- Short time	[°C]	0150 (1 h)			
Electrical data					
Electrical design		DC PNP			
Operating voltage	[V]	1830 DC			
Current consumption	[mA]	< 40			
Protection class		III			
Reverse polarity protection		yes			
Outputs					
Output		2 switching outputs			
Output function		normally open / closed complementary			
Current rating	[mA]	50			
Voltage drop	[V]	< 2.5			
Short-circuit protection		pulsed			
Overload protection		yes			
Environment					
Ambient temperature	[°C]	060			
Storage temperature	[°C]	-2580			
Maximum vessel pressure	[bar]	-116			
Protection		IP 68 / IP 69K			
Tests / approvals	1				
EMC		IEC 61000-6-2 : 2005 IEC 61000-6-4 : 2006 / (open tanks)			



LMT110

LMACE-A12E/QPKG/1/US



		IEC 61000-6-3	: 2006 / (closed tanks)	
Shock resistance		IEC 60068-2-27:	50 g (11 ms)	
Vibration resistance		DIN EN 60068-2-6:	20 g (102000 Hz)	
MTTF	[Years]	469.99		
Mechanical data				
Process connection		G ½ A		
Materials (wetted parts)		PEEK; surface characteristics: Ra < 0.8		
Housing materials		1.4404; PEEK; PA12-GF30; FKM		
Weight	[kg]	0.173		
Displays / operating elen	nents			
Display		Switching status LED yellow		
Electrical connection				
Connection		M12 connector; Gold-plated contacts		
Wiring ² ³ ⁴				
Remarks				
Pack quantity	[piece]		1	

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — LMT110 — 01.04.2014