efectorioo


IE5338

Environment Ambient temperature

Protection

IEBC003BASKG/AS **Inductive sensors**





[°C]

C € cULus		Made in Germany			
Product characteristics	;				
Inductive sensor					
Metal thread M8 x 1					
Connector					
Operation as 3-wire or 2-wire possible					
Sensing range 3 mm; [f] flush mountable					
Electrical data					
Electrical design		3-wire DC PNP; 2-wire DC PNP/NPN			
Operating voltage	[V]	1030 DC (PELV); "supply class 2" to cULus.			
Current consumption	[mA]	< 15			
Protection class		III			
Reverse polarity protection	n	yes			
Outputs					
Output function		normally open			
Voltage drop	[V]	< 3.5			
Minimum load current	[mA]	2; only in 2-wire operation			
Leakage current	[mA]	< 0.5 *)			
Current rating	[mA]	100			
Short-circuit protection		pulsed			
Overload protection		yes			
Switching frequency	[Hz]	800			
Range					
Sensing range	[mm]	3			
Operating distance	[mm]	02.4			
Accuracy / deviations					
Correction factors		mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3			
Hysteresis	[% of Sr]	120			

Tests / approvals				
EMC	EN 61000-4-2 ESD: EN 61000-4-3 HF radiated: EN 61000-4-4 Burst: EN 61000-4-5 Surge: EN 61000-4-6 HF conducted: EN 55011: EN 60947-5-2	4 kV CD / 8 kV AD 10 V/m (802000 MHz) 2 kV 0.5 kV (line to line, Ri: 20hm) 10 V (0.1580 MHz) class B		

0...60

IP 65 / IP 67; with ifm socket duly screwed on

efectorioo

IE5338

IEBC003BASKG/AS



MTTF	[Years]	2046
Mechanical data		
Mounting		flush mountable
Housing materials		Brass special coating; active face: LCP orange; lock nuts: Brass
Installation		BAA
		B A
Tightening torque	[Nm]	≤ 1 (A = 5 mm) ≤ 2 (B)
Weight	[kg]	0.019
Displays / operating ele	ements	
Output status indication	LED	yellow (4 x 90°)
Electrical connection		
Connection		M8 connector
Wiring 4 ••• 1 3		→ 1
Accessories		
Accessories (included)		2 lock nuts
Remarks		
Remarks		*) only in 3-wire operation
Pack quantity	[piece]	1

 $ifm\ electronic\ gmbh\ \bullet\ Friedrichstraße\ 1\ \bullet\ 45128\ Essen\ -\ We\ reserve\ the\ right\ to\ make\ technical\ alterations\ without\ prior\ notice.\ -\ GB\ -\ IE5338\ -\ 28.01.2013$