

**Professionally approved products.**

Product Datasheet

# **10" 7pcs Quick Release Ratchet Crimper Kit**

EN



**RoHS**

**Specifications:**

**Patented quick change die set for easy installation.**

**No tools required for interchange die set.**

**Crimper is easily operated by either  
left or right hand user.**

**Dimensions:**

**1. Insulated terminal:**

**AWG 22-18/16-14/12-10.**

**ø0.5-1.0/1.5-2.5/4.0-6.0mm<sup>2</sup>.**

**2. Non-Insulated terminal:**

**AWG 20-18/16-14/12-10/8.**

**ø 1.5/2.5/6.0/10 mm<sup>2</sup>.**

**3. Open insulated terminal:**

**AWG 20-18/16-14/12-10.**

**ø 0.5-1.0/1.5-2.5/4.0-6.0 mm<sup>2</sup>.**

**4. Open barrel terminal:**

**AWG 22-18/24-22/26-24.**

**ø 0.1-0.25/0.25-0.5/0.5-1.0 mm<sup>2</sup>.**

**5. Open barrel terminal & D-Sub, V3.2:**

**AWG 12/22/8-6.**

**ø 2.5/0.5/730-10 mm<sup>2</sup>.**

**6. Spark plug connector:**

**AWG 17**

**ø 1 mm<sup>2</sup>.**

**Operating Instructions:**

