

AccuSense™ Model ASM

High Accuracy Pressure Transducer



Setra's Model ASM is the highest accuracy transducer for measuring gauge, absolute, compound and vacuum pressure in the AccuSense™ product line. Its $\pm 0.05\%$ FS accuracy is calibrated using the "End Point Method", which improves linearity when compared to competitive transducers which use the "Best Fit Straight Line Method" of calibration. The ASM's calibration is tamper proof by utilizing a SecureCal™ calibration key, which eliminates inadvertent adjustments, while allowing authorized users to adjust the sensor's calibration coefficients for a true sensor calibration. The design of the ASM offers class leading overpressure capability and multiple pressure and electrical fittings for a wide range of applications.

High Accuracy For Demanding Applications

The Model ASM pressure transducer uses a resonant variable capacitance sensor. This sensor is linearized and thermally compensated through a computerized curve fitting algorithm that optimizes the sensor's linearity for maximum accuracy in demanding applications.

Robust Design & Construction for Reliable Service

The Model ASM is designed and built to withstand demanding applications. The laser welded sensor construction, designed with a positive overpressure stop, enables the sensor to resist overpressure conditions up to 10X in all pressure ranges.

Secure and Fast Calibration & Service

The Model ASM is ideal for the Test & Measurement industry because it adheres to the stringent accuracy requirements. In order to make adjustments, the ASM utilizes the SecureCal™ calibration key, providing secure calibration. The SecureCal™ provides the ability to calibrate zero and span coefficients through a simple push button and rotary adjustment dial. The SecureCal™ also offers the option to restore factory defaults for fail-safe sensor calibration.



- **Reliable Testing Data**
- **Minimize Downtime**
- **Reduce Calibration Time**

Model ASM Features:

- High Accuracy: $\pm 0.05\%$ FS
- End Point Method Linearity
- Low Differential Pressure Ranges
- High Overpressure Capability: >10X Range
- Low Thermal Error
- Excellent Stability: <0.15% FS/YR
- Calibrate Using SecureCal™ Calibration Key
- High Line Pressure Capability
- Unidirectional & Bidirectional Models Available

Applications:

- Engine Test Stands
- Particle Test & Analysis
- Industrial (High Accuracy)
- Manifold Pressure
- Refrigeration Testing

AccuSense™ Model ASM

High Accuracy Pressure Transducer



ORDERING INFORMATION


ASM1 - - - - -

| Model | Pressure Ranges | | | | Type | Pressure Port | | Output | | Elec. Termination | | Accuracy | | Option | |
|-----------------|-----------------|---------|-----------------------|--------------------|---------------------------|--|------------------------------|----------------------------------|-----------------------------|-------------------|--|----------|--|--------|--|
| ASM1= Model ASM | PSI | | BAR | | G Gauge | 1F 1/8" NPT Female | 2B 0 to 5 VDC | 03 3 ft, 1m Std Cable | A <±0.05% FS RSS <0.25% TEB | 00 None, Standard | | | | | |
| | Z01P 0 to -14.7 | Z01B -1 | C Compound | 1M 1/8" NPT Male | 2C 0 to 10 VDC | B3 Std 6-Pin Male Bayonet Connector, Std Wiring | B <±0.10% Reading <0.25% TEB | 01 High Overpressure (See Table) | | | | | | | |
| | 015P 0 to 15 | 001B 1 | A Absolute | 2F 1/4" NPT Female | 11 4 to 20 mA | B4 6-Pin Male Bayonet Connector, Optional Wiring (See Op Instructions) | C <±0.1% FS RSS <0.5% TEB | | | | | | | | |
| | 025P 0 to 25 | 002B 2 | V Vacuum ¹ | 2M 1/4" NPT Male | D <±0.1% FS RSS <1.5% TEB | | | | | | | | | | |
| | 050P 0 to 50 | 005B 5 | 'Z01 Range Only | | | | | | | | | | | | |
| | 100P 0 to 100 | 010B 10 | | | | | | | | | | | | | |
| | 150P 0 to 150 | 020B 20 | | | | | | | | | | | | | |
| | 250P 0 to 250 | 040B 40 | | | | | | | | | | | | | |
| | 300P 0 to 300 | 050B 50 | | | | | | | | | | | | | |
| | 500P 0 to 500 | 070B 70 | | | | | | | | | | | | | |
| | 750P 0 to 750 | | | | | | | | | | | | | | |

Example: Part No. ASM1015PG1F2B03A00= ASM Transducer, 0 to 15 PSI pressure range, Gauge, 1/8" NPT Female Pressure Port, 0 to 5 VDC Output, 3ft Cable, ±0.05% FS accuracy, No options

See data sheet for more information on Setra's SecureCal™ Calibration Key.

DIMENSIONS



GENERAL SPECIFICATIONS

| Performance Data | | Physical Description | | | | |
|---|--|--|---|------------------|-------------------------|-----------|
| Zero Offset Position Effect | <0.05%/G (Ranges ≥100 psi) <0.1%/G (Ranges ≤50 psi) | Electrical Terminations | 6-Conductor Cable, Pigtail 6-Pin Bayonet Connector | | | |
| Long-term Stability | <0.10% FS/Year, Typical | Dimensions | See reverse side | | | |
| Response Time to Pressure Input (From 100% to 10% of pressure range) | <10 ms for Voltage Output <80 ms for Current Output | Moisture/Splash Resistance | NEMA 4X (IP65) | | | |
| Unit factory calibrated in vertical position (pressure port downward) | | Weight | 9 oz. (254 g) | | | |
| Environmental Data | | Pressure Fittings | See Ordering Information | | | |
| Temperature Calibrated °F (°C) | -4 to +140 (-20 to +60) | Case Materials | Stainless Steel | | | |
| Operating | -40 to +185 (-40 to +85) | Sensor Description | | | | |
| Storage | -40 to +185 (-40 to +85) | Wetted Materials | 17-4 PH Stainless Steel | | | |
| Vibration | 10g from 1 kHz to 2kHz | Life Cycle Rating | >10^6 Pressure Cycles | | | |
| Higher or lower limits available (consult factory). | | Pressure Media | | | | |
| Electrical Data | | Gases or liquids compatible with 17-4 pH stainless steel. Note: Hydrogen not recommended for use with 17-4 PH stainless steel. | | | | |
| Excitation Range | 9 to 30VDC (5VDC & 4-20 mA output) 15 to 30VDC (10VDC output) | Accuracy Data | | | | |
| Current Consumption | <23 mA | | A | B | C | D |
| Warm-up, Environmental | Within ±0.02% FS after 15 min warm-up time | Accuracy RSS*: End-Point Typ. (BFSL) | <±0.05% FS (<±0.04% FS) | <±0.1% Reading** | <±0.1% FS (<±0.07% FS) | |
| Miswiring | Reverse Excitation Protection | Non-Linearity: End-Point Typ. (BFSL) | <±0.025% FS (±0.015% FS) | | <±0.05% FS (<±0.03% FS) | |
| Signal Output Ranges | 0 to 5 VDC, 0 to 10VDC (4-wire), 4-20mA (2-wire) | Hysteresis | <0.03% FS Typ. | | <±0.03% FS Typ. | |
| Regulatory Data | CE Compliant & RoHS Compliant | Non-Repeatability | <±0.02% FS Typ. | | <±0.02% FS Typ. | |
| Approvals | | Span Setting Tol. | <±0.05% FS | | <±0.01% FS | |
| CE, RoHS | | Zero Offset Tol. | <±0.05% FS Typ. | | <±0.01% FS | |
| | | Thermal Total Error Band (-20°C to 60°C) | <±0.25% FS Typ. | | <±0.5% FS | <±1.5% FS |

^1RSS of Non-Linearity, Hysteresis, and Non-Repeatability.

^2Units calibrated at nominal 70°F. Max thermal error computer from this datum.

^3Operating temperature limits of the electronics only.

*RSS of Non-Linearity, Hysteresis, and Non-Repeatability.
¹Units calibrated at nominal 70°F. Max thermal error computer from this datum.
²Operating temperature limits of the electronics only.
³Calibrated into a 50K ohm load, operable into a 5000 ohm load or greater

Specifications subject to change.
 US Patents # 6,532,834; 6,718,827

PROOF PRESSURE

| Full Scale Range (PSI) | Burst Pressure ¹ (PSI) | Std Proof Pressure ² Option Code "00" | High Proof Pressure Option Code "01" |
|------------------------|-----------------------------------|--|--------------------------------------|
| 0 to 15 | 3,000 | 30 (2x) | 150 (10x) |
| 0 to 25 | 3,000 | 50 (2x) | 250 (10x) |
| 0 to 50 | 8,000 | 100 (2x) | 500 (10x) |
| 0 to 100 | 10,000 | 200 (2x) | 1,000 (10x) |
| 0 to 150 | 10,000 | 300 (2x) | 1,200 (8x) |
| 0 to 200 | 10,000 | 400 (2x) | 1,200 (6x) |
| 0 to 300 | 10,000 | 600 (2x) | 1,500 (5x) |
| 0 to 500 | 10,000 | 800 (1.5x) | 2,000 (4x) |
| 0 to 750 | 10,000 | 1,200 (1.5x) | 2,250 (3x) |
| 0 to 1000 | 10,000 | 1,500 (1.5x) | 3,000 (3x) |

¹ Burst Pressure: The maximum pressure that may be applied to the positive pressure port without rupturing the sensing element.

² Proof Pressure: The maximum recoverable pressure that may be applied without changing performance beyond specification:
 ±0.5% Zero Shift, Typical