



Professionally approved products.

Product Datasheet

50mm Bolt Hole Braked Swivel Castor with Grey Rubber Tyred Wheel, 50kg load capacity



Specification	
Application	General Purpose / Industrial
Features	Ball Bearing Swivel Head
Fixing Centres	Single Bolt Hole
Fixing Hole Size	10mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	50kg
Number of Fixing Holes	1
Overall Height	72mm
Rotation	Swivel & Brake
Tyre Material	Grey Rubber Tyre
Weight Class	Light Duty
Wheel Diameter	50mm
Wheel Width	18mm

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

