




WIRING DIAGRAM				LOCKNUT LN-M12				SPECIFICATIONS																																																																			
								<table><tr><td>RATED OPERATING DISTANCE</td><td>4mm [.157"]</td></tr><tr><td>MOUNTING MODE</td><td>FLUSH</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤ ±10%</td></tr><tr><td>HYSTERESIS</td><td>3-15%</td></tr><tr><td>AMBIENT TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr><tr><td>DC OPERATIONAL CURRENT</td><td>≤ 200 mA</td></tr><tr><td>NO-LOAD CURRENT</td><td>≤ 15 mA</td></tr><tr><td>RESIDUAL CURRENT</td><td>≤ 0.1 mA</td></tr><tr><td>RATED INSULATION VOLTAGE</td><td>≤ 0.5 kV</td></tr><tr><td>SHORT-CIRCUIT PROTECTION</td><td>YES</td></tr><tr><td>MAX. VOLTAGE DROP</td><td>≤ 1.8 V</td></tr><tr><td>WIRE BREAKAGE PROTECTION</td><td>INCORPORATED</td></tr><tr><td>REVERSE POLARITY PROTECTION</td><td>INCORPORATED</td></tr><tr><td>OUTPUT FUNCTION</td><td>3-WIRE, NORMALLY OPEN, NPN</td></tr><tr><td>MAX. SWITCHING FREQUENCY</td><td>≤ 2.0 kHz</td></tr><tr><td>HOUSING MATERIAL</td><td>BRASS, CHROME-PLATED</td></tr><tr><td>ACTIVE FACE MATERIAL</td><td>PLASTIC, PA12-GF20</td></tr><tr><td>CABLE</td><td>ø5.1, PVC</td></tr><tr><td>VIBRATION RESISTANCE</td><td>55 Hz (IN ALL 3 PLANES)</td></tr><tr><td>SHOCK RESISTANCE</td><td>30 g, 11 ms</td></tr><tr><td>DEGREE OF PROTECTION</td><td>IP 67</td></tr><tr><td>SWITCHING STATUS INDICATION</td><td>LED, YELLOW</td></tr></table>				RATED OPERATING DISTANCE	4mm [.157"]	MOUNTING MODE	FLUSH	MIN. REPEAT ACCURACY	≤ 2%	TEMPERATURE DRIFT	≤ ±10%	HYSTERESIS	3-15%	AMBIENT TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	DC OPERATIONAL CURRENT	≤ 200 mA	NO-LOAD CURRENT	≤ 15 mA	RESIDUAL CURRENT	≤ 0.1 mA	RATED INSULATION VOLTAGE	≤ 0.5 kV	SHORT-CIRCUIT PROTECTION	YES	MAX. VOLTAGE DROP	≤ 1.8 V	WIRE BREAKAGE PROTECTION	INCORPORATED	REVERSE POLARITY PROTECTION	INCORPORATED	OUTPUT FUNCTION	3-WIRE, NORMALLY OPEN, NPN	MAX. SWITCHING FREQUENCY	≤ 2.0 kHz	HOUSING MATERIAL	BRASS, CHROME-PLATED	ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20	CABLE	ø5.1, PVC	VIBRATION RESISTANCE	55 Hz (IN ALL 3 PLANES)	SHOCK RESISTANCE	30 g, 11 ms	DEGREE OF PROTECTION	IP 67	SWITCHING STATUS INDICATION	LED, YELLOW																		
RATED OPERATING DISTANCE	4mm [.157"]																																																																										
MOUNTING MODE	FLUSH																																																																										
MIN. REPEAT ACCURACY	≤ 2%																																																																										
TEMPERATURE DRIFT	≤ ±10%																																																																										
HYSTERESIS	3-15%																																																																										
AMBIENT TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																																										
DC OPERATIONAL CURRENT	≤ 200 mA																																																																										
NO-LOAD CURRENT	≤ 15 mA																																																																										
RESIDUAL CURRENT	≤ 0.1 mA																																																																										
RATED INSULATION VOLTAGE	≤ 0.5 kV																																																																										
SHORT-CIRCUIT PROTECTION	YES																																																																										
MAX. VOLTAGE DROP	≤ 1.8 V																																																																										
WIRE BREAKAGE PROTECTION	INCORPORATED																																																																										
REVERSE POLARITY PROTECTION	INCORPORATED																																																																										
OUTPUT FUNCTION	3-WIRE, NORMALLY OPEN, NPN																																																																										
MAX. SWITCHING FREQUENCY	≤ 2.0 kHz																																																																										
HOUSING MATERIAL	BRASS, CHROME-PLATED																																																																										
ACTIVE FACE MATERIAL	PLASTIC, PA12-GF20																																																																										
CABLE	ø5.1, PVC																																																																										
VIBRATION RESISTANCE	55 Hz (IN ALL 3 PLANES)																																																																										
SHOCK RESISTANCE	30 g, 11 ms																																																																										
DEGREE OF PROTECTION	IP 67																																																																										
SWITCHING STATUS INDICATION	LED, YELLOW																																																																										
SHORT-CIRCUIT AND OVERLOAD PROTECTED																																																																											
																																																																											
								SOURCE DRAWING - FOR REFERENCE ONLY																																																																			
<table><tr><td colspan="4">RELATED DOCUMENTS</td></tr><tr><td>1.</td><td></td><td></td><td></td></tr><tr><td>2.</td><td></td><td></td><td></td></tr><tr><td>3.</td><td></td><td></td><td></td></tr><tr><td>4.</td><td></td><td></td><td></td></tr><tr><td colspan="4">MATERIAL</td></tr><tr><td colspan="4">SEE SPECIFICATIONS</td></tr><tr><td colspan="4">FINISH</td></tr><tr><td colspan="4">SEE SPECIFICATIONS</td></tr></table>				RELATED DOCUMENTS				1.				2.				3.				4.				MATERIAL				SEE SPECIFICATIONS				FINISH				SEE SPECIFICATIONS				<table><tr><td colspan="2">3RD ANGLE PROJECTION</td></tr><tr><td></td><td></td></tr><tr><td colspan="2">ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</td></tr><tr><td colspan="2">CONTACT TURCK FOR MORE INFORMATION</td></tr></table>		3RD ANGLE PROJECTION				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		CONTACT TURCK FOR MORE INFORMATION		<table><tr><td colspan="2">THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</td></tr><tr><td>DRFT</td><td>KMY</td></tr><tr><td>DATE</td><td>02/06/12</td></tr><tr><td>APVD</td><td>J.M.</td></tr><tr><td>SCALE</td><td>1=1.0</td></tr><tr><td colspan="2">UNIT OF MEASUREMENT</td></tr><tr><td colspan="2">INCH [MILLIMETER]</td></tr><tr><td colspan="2">DO NOT SCALE THIS DRAWING</td></tr></table>		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		DRFT	KMY	DATE	02/06/12	APVD	J.M.	SCALE	1=1.0	UNIT OF MEASUREMENT		INCH [MILLIMETER]		DO NOT SCALE THIS DRAWING		<table><tr><td colspan="2">TURCK INC</td></tr><tr><td colspan="2">High Technology Sensors and Automation Controls</td></tr><tr><td colspan="2">3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</td></tr></table>		TURCK INC		High Technology Sensors and Automation Controls		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
RELATED DOCUMENTS																																																																											
1.																																																																											
2.																																																																											
3.																																																																											
4.																																																																											
MATERIAL																																																																											
SEE SPECIFICATIONS																																																																											
FINISH																																																																											
SEE SPECIFICATIONS																																																																											
3RD ANGLE PROJECTION																																																																											
ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY																																																																											
CONTACT TURCK FOR MORE INFORMATION																																																																											
THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.																																																																											
DRFT	KMY																																																																										
DATE	02/06/12																																																																										
APVD	J.M.																																																																										
SCALE	1=1.0																																																																										
UNIT OF MEASUREMENT																																																																											
INCH [MILLIMETER]																																																																											
DO NOT SCALE THIS DRAWING																																																																											
TURCK INC																																																																											
High Technology Sensors and Automation Controls																																																																											
3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com																																																																											
<table><tr><td>A</td><td>DRAWING RELEASE</td><td>KMY</td><td>02/06/12</td><td></td></tr><tr><td>REV</td><td>DESCRIPTION</td><td>BY</td><td>DATE</td><td>ECO NO.</td></tr></table>				A	DRAWING RELEASE	KMY	02/06/12		REV	DESCRIPTION	BY	DATE	ECO NO.			<table><tr><td colspan="2">DESCRIPTION</td></tr><tr><td colspan="2">BI 4-G12K-AN6X 3M</td></tr><tr><td colspan="2">IDENTIFICATION NO.</td></tr><tr><td colspan="2">T4670251-1</td></tr><tr><td colspan="2">REV</td></tr><tr><td colspan="2">A</td></tr></table>		DESCRIPTION		BI 4-G12K-AN6X 3M		IDENTIFICATION NO.		T4670251-1		REV		A																																															
A	DRAWING RELEASE	KMY	02/06/12																																																																								
REV	DESCRIPTION	BY	DATE	ECO NO.																																																																							
DESCRIPTION																																																																											
BI 4-G12K-AN6X 3M																																																																											
IDENTIFICATION NO.																																																																											
T4670251-1																																																																											
REV																																																																											
A																																																																											
				FILE: T4670251-1		SHEET 1 OF 1																																																																					