



REMOTE RADIO HEAD DC POWER SUPPLY

Overvoltage Protection for Mobile Broadband Infrastructure

Objective

The DC supply to a remote radio head requires robust and extremely reliable surge protection. Sensitive electronics must be protected from severe overvoltage conditions. The Bourns* SMD Power TVS Diode offers bidirectional overvoltage protection for DC power supplies through a reliable clamping action.

Solution

1 Power TVS (PTVS) Diode: PTVS3-076C-SH

Features & Benefits

The highlighted device supports a standoff voltage of 76 V. Surge voltages are clamped at a low level above this voltage. The device is RoHS compliant* and handles repeated surges with a peak of 3 kA (per IEC 61000-4-5, 8/20 μs). The reduced inductance of the SMD package leads results in superior clamping performance.

Note: Additional voltage and current ratings are available.

Product




PTVS3-076C-SH

Design Kit



TEL-NOTEKIT-1



 $\label{thm:constitute} The schematic shown here illustrates the application protection and does not constitute the complete circuit design.$

Customers should verify actual device performance in their specific applications.

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

BOURNS®

For more information, go to: **www.bourns.com**

or email: protection@bourns.com

Americas: *Tel* +1-951 781-5500

Fax +1-951 781-5700

EMEA: Tel +36 88 520 390

Fax +36 88 520 211

Asia-Pacific: *Tel* +886-2 256 241 17 *Fax* +886-2 256 241 16

COPYRIGHT© 2015 - BOURNS, INC. - 05/15 - PSG - XX/K1537 "Bourns" is a registered trademarks of Bourns, Inc. in the U.S. and other countries.