

**LIGHT FLEXIBLE THERMAL GAP FILLING PADS**


The Aavid SoftFlex series is our most flexible and diverse line of thermal conductive pads. The compressibility and adhesion features enable a dramatic reduction in thermal resistance when mounting. The unique flexibility of the SoftFlex base material provides exceptional contouring and excellent cushioning performance. These defining features ensure that SoftFlex Gap Fillers are ideal for dealing with uneven surfaces, parts with varying heights and devices that require greater flexibility in design, all the while reducing overall stress to the PCB and eliminating tolerances.

**SIZES**

SoftFlex Thermal Interface Pads are available in full 400mm x 200mm sheets that Aavid can cut and shape to suit your needs. They are also available in easy to use 25.4mm x 25.4mm (1" x 1") and 76.2mm x 76.2mm (3" x 3") pads for quick and simple assembly.

**PART NUMBERS**

Part Numbers for Aavid Gap Pads are made up of six sections that represent the product, thickness, adhesion and size. Instructions on how to build your part numbers are available in the document [Building an Aavid Gap Pad Part Number](#).



**FEATURES:**

- High Thermal Conductivity
- Reduced Thermal Resistance
- Wide Range of Hardness
- Flexible, Easy Contouring
- Single & Double Sided Adhesion
- Decreased Strain
- Puncture, Shear and Tear Resistant

**SOFTFLEX PRODUCT LINE DETAILS<sup>1</sup>**

Product Name	SoftFlex A014	SoftFlex B016	SoftFlex C022	SoftFlex D021	SoftFlex E038
<b>Thermal Properties</b>					
Thermal Conductivity (W/mK)	1.4	1.6	2.2	2.1	3.8
Operating Temp. Range (°C)	-40° - 150°	-40° - 150°	-40° - 150°	-40° - 150°	-40° - 150°
Thermal Resistance at 10psi (at % Strain) <sup>2</sup>	6.8 (at 24%)	4.6 (at 39%)	4.0 (at 28%)	5.0 (at 19%)	2.4 (at 18%)
Thermal Resistance at 20psi (at % Strain) <sup>2</sup>	6.0 (at 26%)	3.7 (at 43%)	3.4 (at 33%)	3.9 (at 21%)	2.0 (at 20%)
Thermal Resistance at 40psi (at % Strain) <sup>2</sup>	5.2 (at 30%)	3.6 (at 52%)	2.9 (at 42%)	2.3 (at 25%)	1.9 (at 24%)
<b>Mechanical Properties</b>					
Color	Blue/ Grey	Dark Grey/ Black	Pink/ Grey	Pink/ Light Pink	Grey/ Dark Grey
Adhesion	Single-Sided	Single-Sided	Single-Sided	Single-Sided	Double-Sided
Base Material	Silicone	Silicone	Silicone	Silicone	Silicone
Carrier / Reinforcement	PET Film	PET Film	PET Film	PET Film	PET Film
Hardness (ASTM D2240, Shore 00)	36	37	34	48	71
Density (g/cm <sup>3</sup> )	1.8	2.0	2.9	2.9	3.1
Tensile Strength (kPa)	15	15	22	13	-
Thickness Availability (mm)	1, 2 or 3mm	1, 2 or 3mm	1, 2 or 3mm	1, 2 or 3mm	1, 2 or 3mm
<b>Electrical Properties</b>					
Volume Resistivity (Ω-m)	≥10 <sup>10</sup>	≥10 <sup>10</sup>	≥10 <sup>10</sup>	≥10 <sup>10</sup>	≥10 <sup>10</sup>
Breakdown Voltage (kVAC)	≥10	≥10	≥10	≥10	≥10
Flammability Rating UL94	V-0	V-0	V-1	V-1	V-0


<sup>1</sup> Measurement is for 1mm thickness, information on additional thicknesses is available on request.

<sup>2</sup> Strain is the ratio of the reduction in pad thickness to the initial thickness of the pad. Thermal resistance is measured in (°C x cm<sup>2</sup>/W).



### AAVID GAP FILLING PAD OPTIONS

Aavid’s line of premium thermally conductive gap filling pads are available in three different product lines, each with unique attributes. Each line is available in a variety of thicknesses with multiple types of adhesion and all pads are available in 25.4mm x 25.4mm (1”x 1”) and 76.2mm x 76.2mm (3”x 3”) sizes as well as full sheets or custom shapes.



Aavid’s smart part numbering system is designed to take each attribute in to account and quickly and easily tell you what pad you are ordering at a glance.

### PART NUMBER BREAKDOWN



#### PRODUCT LINE NAME

# A

The three Gap Filler Pad Product Line Names are: *SoftFlex*, *SuperThermal* and *WaveBlocker*.

#### PRODUCT NAME

# B

The Product Name is indicated on the Gap Pad Datasheets. Each Product Name consists of a letter followed by three numerical digits representing the conductivity.

#### THICKNESS (mm)

# C

Thickness is shown as a two digit number with the second digit representing a tenth of a mm. A 1.0mm thickness would be written as “10”.

#### ADHESION

# D

Numbers indicating the type of adhesion:  
“00” = Non Adhesive / “01” = Single Sided / “02” = Double Sided

#### LENGTH (mm)

# E

Four digits representing length in mm with the last digit representing a tenth of a mm. A length of 25.4mm (1 in.) would be written as 0254.

#### WIDTH (mm)

# F

Four digits representing width in mm with the last digit representing a tenth of a mm. A length of 25.4mm (1 in.) would be written as 0254.

### EXAMPLE

A 76.2mm x 76.2mm (3”x 3”) pad of SoftFlex B016 with a 1mm thickness and single side adhesion would have the part number: **SoftFlex-B016-10-01-0762-0762.**