

<b>■</b> Features
■ 2-channel Counter/Frequency Input
■ 32-bit Counter
■ Isolated or Non-isolated Input
Programmable Alarm Output
■ Programmable Digital Filter
■ Programmable Threshold Voltage Level
■ Maximum Frequency of up to 100 kHz
■ Built-in Virtual Battery Backup to Preserve Counter Values (I-7080B(D), M-7080B(D))
■ Dual Watchdog
■ Wide Operating Temperature Range: -25 ~ +75°C
CE FC Kins Z

#### Introduction

The I-7080 offers 2 high speed counter or frequency input channels and 2 digital output channels. Two types of digital input are provided, one for isolated input, and the other is for non-isolated input. The isolated input provides 3750 Vrms isolation voltage and the non-isolated input provides programmable threshold voltage level. The built-in digital filter is valid for both non-isolated and isolated input and can filter out noise where the high/low pulse width is smaller than the minimum high/low width of the digital filter. The maximum count is up to 32-bit and the maximum frequency is up to 100 kHz. The module also provides programmable alarm output with non-isolated open collectors. The M-7080 supports both the Modbus RTU and DCON protocols, which can be configured via software, and all hardware specifications are the same as the I-7080. The functions of the I-7080B are the same as that of the I-7080, except that the I-7080B provides a virtual battery backup function in counter mode.

### System Specifications .

Model	I-7080	I-7080B	M-7080	M-7080B
Model	I-7080D	I-7080BD	M-7080D	M-7080BD
Communication				
Interface	RS-485			
Format	(N, 8, 1) (N, 8, 2) (E, 8, 1) (O, 8, 1)			
Baud Rate	1200 ~ 115200 bps			
Protocol	DCON Modbus RTU, DCON			DCON
Dual Watchdog	Yes, Module (	1.6 Seconds), C	ommunication	(Programmable)
LED Indicators/Display				
System LED Indicator	Yes, 1 LED as Power/Communication Indicator			
I/O LED Indicators	-			
7-Segment LED Display	-			
7-Segment LED Display	Yes			
Isolation				
Intra-module Isolation, Field-to-Logic	3000 VDC			
EMS Protection				
ESD (IEC 61000-4-2)	±4 kV Contact for each Terminal			
EFT (IEC 61000-4-4)	±4 kV for Power Line			
Surge (IEC 61000-4-5)	±0.5 kV for Power Line			
Power	Power			
Reverse Polarity Protection	Yes			
Input Range	10 ~ 30 VDC	24 ~ 30 VDC	10 ~ 30 VDC	24 ~ 30 VDC
Consumption	2.0 W			
Consumption	2.2 W			
Mechanical				
Dimensions (W x L x H)	72 mm x 123 mm x 35 mm			
Installation	DIN-Rail or Wall Mounting			
Environment				
Operating Temperature	-25 ~ +75°C			
Storage Temperature	-40 ~ +85°C			
Humidity	10 ~ 95% RH	I, Non-condens	ing	

#### Applications


- Building Automation
- Machine Automation
- Remote Diagnosis

- Factory Automation
- Remote Maintenance
- Testing Equipment


## ■ I/O Specifications \_\_\_\_\_

		1-7080	I-7080B	M-7080	M-7080B	
Model		I-7080D				
Digital Input		1-70000	1-700000	WI-7000D	W-7000B	
Channels		2				
Contact		Wet				
Sink/Source (NPN/PNP)		Sink				
Simpodaree (iii ii)	Isolated	+3.5 ~ +30 Vpc				
On Voltage Level	Non-isolated	+2.4 ~ +5 VDC				
Off Voltage Level		+1 Vpc Max.				
Programmable Filte	Pr .	2 µs to 65 ms				
Programmable Thr		'				
Individual Channel Configuration		No.				
Counter/Encoder-bits		32-bit				
Counter Mode		Up				
Encoder Mode		-				
Frequency Mode		Yes				
Virtual Battery Backup		-	Yes	_	Yes	
Frequency Accuracy		1 Hz or 10 Hz				
Max. Speed		100 KHz				
Digital Output						
Channels		2				
Туре		Open Collector				
Sink/Source (NPN/PNP)		Sink				
Load Voltage		+3.5 ~ +30 Vpc				
Max. Load Current		30 mA/Channel				
Max. Load Current		30 may Cha	IIICI			

### Internal I/O Structure \_



# **■ Pin Assignments** .



#### Wire Connections -

Counter Type V	Vire Connection		
Isolation	Non-isolation		
Counter Input+	Counter Input — ☐ ☐ ☐ INX Gate Control — ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐		
Frequency Type Wire Connection			
Isolation	Non-isolation		
Frequency Input+ $ \square \Leftrightarrow \square \Leftrightarrow \square$ INx+ Frequency Input- $ \square \Leftrightarrow \square \Leftrightarrow \square \Leftrightarrow \square \Leftrightarrow \square$ GATEx+ Not used $ \square \Leftrightarrow \square \Leftrightarrow \square \Leftrightarrow \square \Leftrightarrow \square \Leftrightarrow \square$	Frequency Input+ —  Not used —  Frequency Input- D.GND		

Output Type	ON State Readback as 1	OFF State Readback as 0	
Resistance Load	+ W DOX - (B)GND	+	
Inductance Load	+ DOX	+ DOX	

# Ordering Information -

I-7080 CR	2-channel Counter/Frequency Input Module with DCON Protocol (Blue Cover) (RoHS)	
I-7080-G CR	2-channel Counter/Frequency Input Module with DCON Protocol (Gray Cover) (RoHS)	
I-7080D CR	I-7080 with 7-segment LED Display (Blue Cover) (RoHS)	
I-7080B-G CR	2-channel Counter/Frequency Input Module with DCON Protocol with Virtual Battery Backup (Gray Cover) (RoHS)	
I-7080BD-G CR	I-7080B with 7-segment LED Display (Gray Cover) (RoHS)	
M-7080-G CR	2-channel Counter/Frequency Input Module with DCON and Modbus Protocol (Gray Cover) (RoHS)	
M-7080D-G CR	M-7080 with 7-segment LED Display (Gray Cover) (RoHS)	
M-7080B-G CR	2-channel Counter/Frequency Input Module with DCON and Modbus Protocol with Virtual Battery Backup (Gray Cover) (RoHS)	
M-7080BD-G-G CR	M-7080B with 7-segment LED Display (Gray Cover) (RoHS)	

### Accessories .



SG-770 CR

7-channel Differential or 14-channel Single-ended Surge Protector (RoHS)