

On the bottom menu bar, click **Page by Page** to access a page index or **Pages-at-a-Glance** to access a section index. View single pages in order by clicking **Previous** or **Next**. For improved print clarity, click **Page in PDF**. To **Print a PDF** be sure to select **Current Page** in your print monitor. Click **Email to a friend** to send a page to a third party. **Search** by 9 digit (54.003.7553) or 5-digit (54003) part number, series (WKC), or type of product (PCB connectors).

PC board connectors, rising cage clamp system Spacing: 5.00/5.08/10.00 mm

wiecon PCB

Rated cross section:
2.5 mm²

Rated current:
16 A

Connection range:
0.14 – 4.0 mm² solid/
0.14 – 2.5 mm² fine stranded

Rated voltages:
Spacing: 5.00/5.08 mm VDE 0110
250 V/4 kV/3 – Overvoltage category III
*690 V/4 kV/2 – Overvoltage category II
1000 V/4 kV/1 – Overvoltage category I

Rated voltages:
Spacing: 10.00 mm VDE 0110
690 V/8 kV/3 – Overvoltage category III
1000 V/8 kV/2 – Overvoltage category II
1000 V/8 kV/1 – Overvoltage category I

* max. 690 V for ungrounded networks or expected overvoltage ≤ 4 kV

Rated voltages VDE 0110


UL ratings

field/factory wiring


CSA ratings

Approvals


Spacing: 5.00/5.08 mm, without insulating plate





with insulating plate, without fixing bolts



Spacing: 10.00 mm, without insulating plate



with insulating plate, without fixing bolts



Solder pin 0.9 x 0.9 mm
Bore hole Ø 1.3 mm

Type 8191/8291


wire horizontal to PC board
(with exposed test point)

No. 22 – 12 AWG

300 V 20/30 A

No. 22 – 12 AWG

300 V 25 A



Std pack	G	T	Poles	Part no. unmarked without insulating plate	Part no. marked without insulating plate	Part no. unmarked with insulating plate with fixing bolts	Part no. marked with insulating plate with fixing bolts
Spacing: 5.00 mm							
100	10.85	5	2	25.161.0253.0	25.160.0253.0	25.171.0253.0	25.170.0253.0
100	15.85	10	3	25.161.0353.0	25.160.0353.0	25.171.0353.0	25.170.0353.0
50	20.85	15	4	25.161.0453.0	25.160.0453.0		
50	25.85	20	5	25.161.0553.0	25.160.0553.0		
50	30.85	25	6	25.161.0653.0	25.160.0653.0		
50	35.85	30	7	25.161.0753.0	25.160.0753.0		
50	40.85	35	8	25.161.0853.0	25.160.0853.0		
50	45.85	40	9	25.161.0953.0	25.160.0953.0		
50	50.85	45	10	25.161.1053.0	25.160.1053.0		
50	55.85	50	11	25.161.1153.0	25.160.1153.0		
50	60.85	55	12	25.161.1253.0	25.160.1253.0		
50	65.85	60	13	25.161.1353.0	25.160.1353.0		
50	70.85	65	14	25.161.1453.0	25.160.1453.0		
50	75.85	70	15	25.161.1553.0	25.160.1553.0		

	50	80.85	75	16	25.161.1653.0	25.160.1653.0		
17 to 24pole upon request								
Spacing: 5.08 mm								
	100	11.01	5.08	2	25.163.0253.0		25.173.0253.0	25.172.0253.0
	100	16.09	10.16	3	25.163.0353.0		25.173.0353.0	25.172.0353.0
	50	21.17	15.24	4	25.163.0453.0			
	50	26.25	20.32	5	25.163.0553.0			
	50	31.33	25.40	6	25.163.0653.0			
	50	36.41	30.48	7	25.163.0753.0			
	50	41.49	35.56	8	25.163.0853.0			
	50	46.57	40.64	9	25.163.0953.0			
	50	51.65	45.72	10	25.163.1053.0			
	50	56.73	50.80	11	25.163.1153.0			
	50	61.81	55.88	12	25.163.1253.0			
	50	66.89	60.96	13	25.163.1353.0			
	50	71.97	66.04	14	25.163.1453.0			
	50	77.05	71.12	15	25.163.1553.0			
	50	82.13	76.20	16	25.163.1653.0			
17 to 24pole upon request								
Spacing: 10.00 mm								
	100	15.85	10	2	25.169.0253.0	25.168.0253.0	25.169.6253.0	25.168.6253.0
4 to 12pole upon requ.	50	25.85	20	3	25.169.0353.0	25.168.0353.0	25.169.6353.0	25.168.6353.0

344