





MALE END VIEW

FEMALE END VIEW




- 1 = WHITE
- 2 = BLACK
- 3 = GREEN
- 4 = RED
- 5 = ORANGE
- 6 = BLUE
- 7 = BROWN
- 8 = YELLOW
- 9 = VIOLET
- 10 = GRAY
- 11 = PINK
- 12 = TAN
- 13 = WHITE/BLACK
- 14 = WHITE/GREEN
- 15 = WHITE/RED
- 16 = WHITE/BLUE



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	NYLON or PBT/GRAY
MOLDED HEAD MATERIAL/COLOR	TPU/BLACK
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	3.0 A
RATED VOLTAGE [V]	300 V
OUTER JACKET MATERIAL/COLOR	PVC PLTC/BLUE
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	16x22 AWG
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	IEC IP67

\* METERS  
+100mm\*/-0mm OR 4%  
(WHICHEVER IS GREATER)  
SEE NOTE 1



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "\*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<b>TURCK INC</b> High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL SEE SPECIFICATIONS	DRFT RDS DATE 09/09/09	DESCRIPTION CSNWM CKNM 16-16-*		REV C
FINISH SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	DSGN SCALE 1=1.3	IDENTIFICATION NO.		FILE: 777001371
		UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b>		SHEET 1 OF 1	
DO NOT SCALE THIS DRAWING					

C	DRAWING PROCESSED AS PART OF ECO 33971	CBM	04/06/11	33971
REV	DESCRIPTION	BY	DATE	ECO NO.