

# Guarded IP68 Sealed Foot Switch



<b>Degree of protection</b>	IP68
<b>Materials of Construction</b>	Cast Aluminium Housing.
<b>Colour</b>	Black body, silver treadle & Alert Orange guard.
<b>Cable Connection</b>	1 x M20 entry.
<b>Contact Action</b>	SPDT momentary.
<b>Electrical Rating</b>	16A 125-250V a.c. 0.375kW 125-250V a.c, 250V a.c. max.
<b>Features &amp; Benefits</b>	Waterproof sealing suits harsh environments. Non-skid feet to minimise movement. 4 holes provided for solid mounting to floor or equipment.
<b>Weight</b>	2.7kg
<b>Size</b>	(See below)

