

PLUG-IN RELAY 3CO RELAY OR LED 38MM, 230V AC



Figure similar

General technical data:

Supply voltage frequency for auxiliary and control current circuit Rated value		
• minimum	Hz	50
• maximum	Hz	60
<b>Type of voltage</b>		AC
<b>Control supply voltage</b>		
• at AC		
— at 50 Hz Rated value		
— minimum	V	230
— maximum	V	230
— at 60 Hz Rated value		
— minimum	V	230
— maximum	V	230
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		3
Operating current of the auxiliary contacts		
• at AC-15		

— at 230 V

	A	5
Design of the switching function positively driven		No
Switching behavior		monostable

#### Mechanical data:

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		No
Width	mm	35.5
Height	mm	36.5
Depth	mm	69

#### Certificates/ approvals:

##### General Product Approval

##### Declaration of Conformity



#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZX:MT326230>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:MT326230>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=LZX:MT326230&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZX:MT326230&lang=en)

last modified:

15.10.2015