



Professionally approved products.


## Datasheet

### Sealed Miniature Toggle






RS Stock number 448-0898

#### Number of Poles/Dimensions

		A	B	C
<b>1</b>	<b>SPDT</b>  2 Comm. 1 3	5,08 mm	8,13 mm	8,64 mm
<b>2</b>	<b>DPDT</b>  2 Comm. 5 Comm. 1 3 4 6	9,14 mm	8,13 mm	8,64 mm




#### Electrical Functions

			
<b>1</b>	on	none	on
<b>2</b>	on	none	(on)
<b>3</b>	on	off	on
<b>4</b>	(on)	off	(on)
<b>5</b>	on	off	(on)
	 <p>SPDT DPDT 2 5 1 3 4 6</p>	open	 <p>SPDT DPDT 2 5 1 3 4 6</p>


# Professionally approved products. Datasheet

## Actuators


**N - ROUND TOGGLE**




**N2 - ROUND TOGGLE**




**N3 - ROUND TOGGLE**




**N4 - ROUND TOGGLE**




**N5 - ROUND TOGGLE**



**LK - LOCKING LEVER**





**LK1 - LOCKING LEVER**





# Professionally approved products. Datasheet

## Bushing



**F1 - THREADED**  
**F2 - UNTHREADED**





**F3 - THREADED**  
**F4 - UNTHREADED**



**B1 - THREADED**  
**B2 - UNTHREADED**



**B3 - THREADED**  
**B4 - UNTHREADED**



## Sealing



**E**


# Professionally approved products. Datasheet

## Terminations


For single pole

For double pole


ST




PC




ST



PC




W5





**Dim. A**  
**W5 .600 (15.24)**


H9  
SPDT



H9S




P.C. LAYOUT





Part N° shown: 2A11-N2F2H9AE


H9  
DPDT



H9S




P.C. LAYOUT





Part N° shown: 2A21-N2F2H9AE


V9  
SPDT



V9S




P.C. LAYOUT





Part N° shown: 2A11-N2F2V9AE

V9  
DPDT



V9S



P.C. LAYOUT





Part N° shown: 2A21-N2F2V9AE


# Professionally approved products. Datasheet

## Terminations

**U2**  
**SPDT**





**P.C. LAYOUT**




**Part N° shown: 2A11-N2F2U2AE**

**U2**  
**DPDT**



**P.C. LAYOUT**



**Part N° shown: 2A21-N2F2U2AE**

## Contact Materials – Contact Ratings

- S** **Moving Contacts:** coin silver, silver plated  
**Terminals:** brass, silver plated  
**Rating:** 3 Amps @ 120 VAC or 28 VDC  
1.5 Amps @ 250 VAC
- A** **Moving Contacts:** brass with gold plate over nickel plate  
**Terminals:** brass with gold plate over nickel plate  
**Rating:** 0.4 Volts/Amps max @ 20 VAC or DC max
- G** **Moving Contacts:** coin silver gold plated  
**Terminals:** brass silver plated and gold plated  
**Note:** G option used for either "high" (2 Amps @ 250 VAC) or "low" (0.4 Volts/Amps max) contact rating (one exclude the other)
- K** **Moving Contacts:** copper alloy with gold plating over nickel plating  
**Terminals:** copper alloy with gold plating over nickel plating  
**Rating:** 0.4 Volts/Amps max @ 20 Volts max (AC or DC)