

För icke direkt toleranssatta mått gäller toleransklass
General tolerances if not otherwise stated

--



NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.


Övriga generella toleranser enligt ritning 4100-4644.
Additional general tolerances in accordance with drawing 4100-4644.

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.



Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
10	P2751	Ändrad enligt kund/ Changed according the customer	091103	SE

FÖRSPÄNNING: 220 N ± 40 N MED TOLK
 Ø 2.95 I URTAG FÖR 10 mm²
 PRELOAD: 220 N ± 40 N WITH GAUGE
 Ø 2.95 IN NEST FOR 10 mm²

Material		Behandling/Treatment			Status Frisläppt	
Konstr./Design CF	Ritad/Drawn TGW	Datum/Date 2009-11-03	Skala/Scale 1:2	Kontr./Checked IP	Godk./Approved NE	Änne/Blank
pressmaster [®] 			Benämning/Denomination KRIMPTÅNG 297-2935 CRIMPING TOOL		Vikt/Weight, gram	Art grp 012
					Ritn nr./Drawing no 43002430	REV 010