



Datasheet

## Countersunk Ankerbolt

### Product

A Countersunk self tapping anchor with a Torx drive, for use in concrete, brick and some natural stone

### Material



Carbon Steel, Hardened and heat treated

### Standard colour

Zinc

### Finish

Zinc Plated min 5µm



Part Number	Outside Diam	Length	Drill Diameter	Max Fixture Thickness	Minimum Hole Depth	Torx Drive	Rec. Tensile Resistance	Rec. Shear Resistance	Tightening Torque
	A	B							
	mm	mm	mm	mm	mm		kN	kN	Nm
9086725	8	75	6	45	40	T30	0.8	0.8	15
9086729	8	100	6	55	55	T30	1.9	3.6	25
9086738	8	130	6	85	55	T30	1.9	3.6	25
9086731	10	60	8	20	55	T45	2.9	8.6	40
9086735	10	75	8	35	55	T45	2.9	8.6	40
9086744	10	100	8	60	55	T45	2.9	8.6	40
9086747	12	60	10	10	70	T50	4.4	14.3	60
9086741	12	75	10	25	70	T50	4.4	14.3	60
9086750	12	100	10	50	70	T50	4.4	14.3	60