## **SIEMENS**

## Data sheet

## 6ES7211-1AE40-0XB0

SIMATIC S7-1200, CPU 1211C, COMPACT CPU, DC/DC/DC, ONBOARD I/O: 6 DI 24V DC; 4 DO 24 V DC; 2 AI 0 - 10V DC, POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA MEMORY: 50 KB



General information	
Product type designation	CPU 1211C DC/DC/DC
Firmware version	V4.1
Engineering with	
Programming package	STEP 7 V13 SP1 or higher
Display	
with display	No
Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Load voltage L+	
● Rated value (DC)	24 V
<ul> <li>permissible range, lower limit (DC)</li> </ul>	20.4 V
<ul> <li>permissible range, upper limit (DC)</li> </ul>	28.8 V

Input current	
Current consumption (rated value)	300 mA; CPU only
Current consumption, max.	900 mA; CPU with all expansion modules
Inrush current, max.	12 A; at 28.8 V DC
Encoder supply	
24 V encoder supply	
• 24 V	L+ minus 4 V DC min.
Output current	
for backplane bus (5 V DC), max.	750 mA; Max. 5 V DC for CM
Power loss	
Power loss, typ.	8 W
Memory	
Type of memory	RAM
Work memory	
• integrated	50 kbyte
• expandable	No
Load memory	
• integrated	1 Mbyte
<ul> <li>Plug-in (SIMATIC Memory Card), max.</li> </ul>	with SIMATIC memory card
Backup	
• present	Yes; maintenance-free
<ul><li>without battery</li></ul>	Yes
CPU processing times	
for bit operations, typ.	0.085 μs; / instruction
for word operations, typ.	1.7 μs; / instruction
for floating point arithmetic, typ.	2.3 μs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
ОВ	
Number, max.	Limited only by RAM for code
Data areas and their retentivity	
retentive data area in total (incl. times, counters, flags), max.	10 kbyte
Flag	
Number, max.	4 kbyte; Size of bit memory address area
Local data	
• per priority class, max.	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB

A deluces are	
Address area	
Process image	1 librato
• Inputs, adjustable	1 kbyte
Outputs, adjustable	1 kbyte
Hardware configuration	
Number of modules per system, max.	3 communication modules, 1 signal board
Time of day	
Clock	
<ul><li>Hardware clock (real-time clock)</li></ul>	Yes
Backup time	480 h; Typical
• Deviation per day, max.	+/- 60 s/month at 25 °C
Digital inputs	
Number of digital inputs	6; Integrated
<ul> <li>of which inputs usable for technological functions</li> </ul>	3; HSC (High Speed Counting)
integrated channels (DI)	6
m/p-reading	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	6
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
• for signal "1"	15 VDC at 2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— parameterizable	Yes
for counter/technological functions	
— parameterizable	Single phase : 3 @ 100 kHz, differential: 3 @ 80 kHz
Cable length	
• shielded, max.	500 m; 50 m for technological functions
• unshielded, max.	300 m; For technological functions: No
Digital outputs	
Number of digital outputs	4
<ul><li>of which high-speed outputs</li></ul>	4; 100 kHz Pulse Train Output
integrated channels (DO)	4

Limitation of inductive shutdown voltage to	L+ (-48 V)
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Output voltage	
● for signal "0", max.	0.1 V; with 10 kOhm load
• for signal "1", min.	20 V
Output current	
● for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", max.	1 μs
• "1" to "0", max.	5 μs
Switching frequency	
• of the pulse outputs, with resistive load, max.	100 kHz
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
Analog inputs	
Number of analog inputs	2
integrated channels (AI)	2; 0 to 10V
Input ranges	
Voltage	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
<ul><li>Input resistance (0 to 10 V)</li></ul>	≥100k ohms
Cable length	
• shielded, max.	100 m; twisted and shielded
Analog outputs	
Number of analog outputs	0
Analog value generation	
Integration and conversion time/resolution per channel	
<ul> <li>Resolution with overrange (bit including sign),</li> </ul>	10 bit
max.	
<ul> <li>Integration time, parameterizable</li> </ul>	Yes
<ul><li>Conversion time (per channel)</li></ul>	625 μs
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
1. Interface	

Interface type	PROFINET
Physics	Ethernet
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Functionality	
PROFINET IO Controller	Yes
PROFINET IO Device	Yes
Open IE communication	Yes
Web server	Yes
PROFINET IO Controller	
Transmission rate, max.	100 Mbit/s
Services	
— Number of connectable IO Devices, max.	16
PROFINET IO Device	
Services	
— Shared device	Yes
Number of IO Controllers with shared	2
device, max.	
Protocols Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 required
AS-Interface	Yes
Protocols (Ethernet)	163
Tiotocois (Ethernet)	
▲ TCD/ID	Yes
TCP/IP  Further protocols	Yes
Further protocols	
	Yes
Further protocols  • MODBUS	
Further protocols  • MODBUS  Communication functions	
Further protocols  • MODBUS  Communication functions	
Further protocols  • MODBUS  Communication functions  S7 communication	Yes
Further protocols  • MODBUS  Communication functions  \$7 communication  • supported	Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server	Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client	Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication	Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP	Yes Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP  • ISO-on-TCP (RFC1006)	Yes Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP  • ISO-on-TCP (RFC1006)  • UDP	Yes Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP  • ISO-on-TCP (RFC1006)  • UDP  Web server	Yes Yes Yes Yes Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP  • ISO-on-TCP (RFC1006)  • UDP  Web server  • supported	Yes Yes Yes Yes Yes Yes Yes Yes Yes
Further protocols  • MODBUS  Communication functions  S7 communication  • supported  • as server  • as client  Open IE communication  • TCP/IP  • ISO-on-TCP (RFC1006)  • UDP  Web server  • supported  • User-defined websites	Yes Yes Yes Yes Yes Yes Yes Yes Yes

Test commissioning functions	Test commissioning functions	
Status/control		
Status/control variable	Yes	
Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters	
Forcing		
<ul><li>Forcing</li></ul>	Yes	
Diagnostic buffer		
• present	Yes	
Traces		
Number of configurable Traces	2; Up to 512 KB of data per trace are possible	
Integrated Functions		
Number of counters	3	
Counting frequency (counter) max.	100 kHz	
Frequency meter	Yes	
controlled positioning	Yes	
Number of position-controlled positioning axes, max.	8	
Number of positioning axes via pulse-direction interface	4; With integrated DO	
PID controller	Yes	
Number of alarm inputs	4	
Number of pulse outputs	4	
Limit frequency (pulse)	100 kHz	
Potential separation		
Potential separation digital inputs		
<ul> <li>Potential separation digital inputs</li> </ul>	500V AC for 1 minute	
<ul> <li>between the channels, in groups of</li> </ul>	1	
Potential separation digital outputs		
<ul> <li>Potential separation digital outputs</li> </ul>	Yes	
<ul><li>between the channels</li></ul>	No	
<ul> <li>between the channels, in groups of</li> </ul>	1	
Interference immunity against discharge of static electric	icity	
<ul> <li>Interference immunity against discharge of static electricity acc. to IEC 61000-4-2</li> </ul>	Yes	
Test voltage at air discharge	8 kV	
Test voltage at contact discharge	6 kV	
Interference immunity to cable-borne interference		
<ul> <li>Interference immunity on supply lines acc. to IEC 61000-4-4</li> </ul>	Yes	
<ul> <li>Interference immunity on signal cables acc. to IEC 61000-4-4</li> </ul>	Yes	

Interference immunity against voltage curge	
Interference immunity against voltage surge	Yes
• on the supply lines acc. to IEC 61000-4-5	
Interference immunity against conducted variable distur	
<ul> <li>Interference immunity against high-frequency radiation acc. to IEC 61000-4-6</li> </ul>	Yes
Emission of radio interference acc. to EN 55 011	
<ul> <li>Limit class A, for use in industrial areas</li> </ul>	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
Marine approval	
Marine approval	Yes
Ambient conditions	
Free fall	
<ul> <li>Drop height, max. (in packaging)</li> </ul>	0.3 m; five times, in dispatch package
Ambient temperature during operation	
● min.	-20 °C
• max.	60 °C
<ul> <li>horizontal installation, min.</li> </ul>	-20 °C
<ul> <li>horizontal installation, max.</li> </ul>	60 °C
<ul> <li>vertical installation, min.</li> </ul>	
<ul><li>vertical installation, max.</li></ul>	-20 °C
	-20 °C 50 °C
Ambient temperature during storage/transportation	
Ambient temperature during storage/transportation  • min.	
	50 °C
• min.	50 °C -40 °C
min.     max.	50 °C -40 °C
<ul><li>min.</li><li>max.</li></ul> Air pressure acc. to IEC 60068-2-13	50 °C -40 °C 70 °C
<ul> <li>min.</li> <li>max.</li> </ul> Air pressure acc. to IEC 60068-2-13 <ul> <li>Storage/transport, min.</li> </ul>	50 °C  -40 °C  70 °C  660 hPa
<ul> <li>min.</li> <li>max.</li> </ul> Air pressure acc. to IEC 60068-2-13 <ul> <li>Storage/transport, min.</li> <li>Storage/transport, max.</li> </ul>	50 °C  -40 °C  70 °C  660 hPa  1 080 hPa
<ul> <li>min.</li> <li>max.</li> </ul> Air pressure acc. to IEC 60068-2-13 <ul> <li>Storage/transport, min.</li> <li>Storage/transport, max.</li> <li>permissible operating height</li> </ul>	50 °C  -40 °C  70 °C  660 hPa  1 080 hPa

<ul><li>Vibrations</li></ul>	2G wall mounting, 1G DIN rail
<ul> <li>Operation, tested according to IEC 60068-2-6</li> </ul>	Yes
Shock test	
• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
Extended ambient conditions	
Pollutant concentrations	
— SO2 at RH < 60% without condensation	S02: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
Configuration	
Programming	
Programming language	
— LAD	Yes
— FBD	Yes
— SCL	Yes
Cycle time monitoring	
• adjustable	Yes
Dimensions	
Width	90 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	370 g
last modified:	13.01.2016