

Product type designation

Product description

IE connecting cable IE FC RJ45-180 / IE FC RJ45-180

Flexible plug-in cable (4-core), preferred length, preassembled with two IE FC RJ45 connectors 2x2
IE CONNECTING CABLE IE FC RJ45 PLUG-180/IE FC RJ45 PLUG-180; IE FC TRAILING CABLE GP PREASS. W. 2X IE FC RJ45 PLUG 180; LENGTH 5.0 M



Suitability for use	For connecting Industrial Ethernet stations with an RJ45 interface
Cable length	5 m
Electrical data	
Damping ratio per length	
• at 10 MHz / maximum	0.06 dB/m
• at 100 MHz / maximum	0.2 dB/m
Impedance	
• at 1 MHz ... 100 MHz	100 Ω
Relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	5 %
Near-end crosstalk per length	
• at 1 MHz ... 100 MHz	0.5 dB/m
Transfer impedance per length / at 10 MHz	20 mΩ/m
Loop resistance per length / maximum	120 mΩ/m
Operating voltage	
• RMS value	100 V

NVP value in percent	66 %
----------------------	------

Mechanical data

Number of electrical cores	4
Design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
Core diameter <ul style="list-style-type: none"> • of AWG22 core 	0.75 mm
Outer diameter <ul style="list-style-type: none"> • of inner conductor • of the wire insulation • of the inner sheath of the cable • of cable sheath 	0.75 mm 1.5 mm 3.9 mm 6.5 mm
Symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
Material <ul style="list-style-type: none"> • of the wire insulation • of the inner sheath of the cable • of cable sheath 	PE PVC PVC
Color <ul style="list-style-type: none"> • of the insulation of data wires • of cable sheath 	white/yellow/blue/orange green
Bending radius <ul style="list-style-type: none"> • with single bend / minimum permissible • with multiple bends / minimum permissible • with continuous bending 	32.5 mm 58.5 mm 100 mm
Number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
Tensile load / maximum	150 N
Weight per length	68 kg/km

Permitted ambient conditions

Ambient temperature <ul style="list-style-type: none"> • during operation • during storage • during transport • during installation • Note 	-25 ... +75 °C -25 ... +75 °C -25 ... +75 °C -10 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN VDE 0472
Burning behavior	flame resistant according to UL 1685 (CSA FT 4)
Chemical resistance <ul style="list-style-type: none"> • to mineral oil • to grease 	conditional resistance Conditional resistance

• to water	conditional resistance
Radiological resistance / to UV radiation	resistant

Product properties, functions, components / general

Product feature	
• halogen-free	No
• silicon-free	Yes

Standards, specifications, approvals

UL/ETL listing / 300 V Rating	Yes; c(UL)us, CMG / PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes
Certificate of suitability	
• RoHS conformity	Yes
Standard for structured cabling	Cat5e
• Marine classification association / American Bureau of Shipping Europe Ltd. (ABS)	No
• Marine classification association / Bureau Veritas (BV)	No
• Marine classification association / Det Norske Veritas (DNV)	No
• Marine classification association / Germanische Lloyd (GL)	No
• Marine classification association / Lloyds Register of Shipping (LRS)	No
• Marine classification association / Nippon Kaiji Kyokai (NK)	No
• Marine classification association / Polski Rejestr Statkow (PRS)	No

Further Information / Internet Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified: 15.02.2016