

SIMATIC S7-1200, CPU 1215C, COMPACT CPU, DC/DC/DC, 2 PROFINET PORT, ONBOARD I/O: 14 DI 24V DC; 10 DO 24V DC 0.5A 2 AI 0-10V DC, 2 AO 0-20MA DC, POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA MEMORY: 125 KB



General information	
Product type designation	CPU 1215C DC/DC/DC
Firmware version	V4.1
Engineering with	
<ul style="list-style-type: none"> Programming package 	STEP 7 V13 SP1 or higher
Display	
with display	No
Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> 24 V DC 	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Load voltage L+	
<ul style="list-style-type: none"> Rated value (DC) 	24 V
<ul style="list-style-type: none"> permissible range, lower limit (DC) 	5 V
<ul style="list-style-type: none"> permissible range, upper limit (DC) 	250 V

Input current	
Current consumption (rated value)	500 mA; CPU only
Current consumption, max.	1 500 mA; CPU with all expansion modules
Inrush current, max.	12 A; at 28.8 V DC
Encoder supply	
24 V encoder supply	
• 24 V	L+ minus 4 V DC min.
Output current	
for backplane bus (5 V DC), max.	1 600 mA; Max. 5 V DC for SM and CM
Power loss	
Power loss, typ.	12 W
Memory	
Type of memory	RAM
Work memory	
• integrated	125 kbyte
• expandable	No
Load memory	
• integrated	4 Mbyte
• Plug-in (SIMATIC Memory Card), max.	with SIMATIC memory card
Backup	
• present	Yes; maintenance-free
• without battery	Yes
CPU processing times	
for bit operations, typ.	0.085 µs; / instruction
for word operations, typ.	1.5 µs; / instruction
for floating point arithmetic, typ.	2.3 µs; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
OB	
• Number, max.	Limited only by RAM for code
Data areas and their retentivity	
retentive data area in total (incl. times, counters, flags), max.	10 kbyte
Flag	
• Number, max.	8 kbyte; Size of bit memory address area
Local data	
• per priority class, max.	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB

Address area	
Process image	
• Inputs, adjustable	1 kbyte
• Outputs, adjustable	1 kbyte
Hardware configuration	
Number of modules per system, max.	3 comm. modules, 1 signal board, 8 signal modules
Time of day	
Clock	
• Hardware clock (real-time clock)	Yes
• Backup time	480 h; Typical
• Deviation per day, max.	+/- 60 s/month at 25 °C
Digital inputs	
Number of digital inputs	14; Integrated
• of which inputs usable for technological functions	6; HSC (High Speed Counting)
integrated channels (DI)	14
m/p-reading	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	14
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
• for signal "1"	15 VDC at 2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— parameterizable	Yes
for counter/technological functions	
— parameterizable	Single phase : 3 at 100 kHz & 3 at 30 kHz, differential: 3 at 80 kHz & 3 at 30 kHz
Cable length	
• shielded, max.	500 m; 50 m for technological functions
• unshielded, max.	300 m; For technological functions: No
Digital outputs	
Number of digital outputs	10
• of which high-speed outputs	4; 100 kHz Pulse Train Output

integrated channels (DO)	10
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
Output delay with resistive load	
• "0" to "1", max.	1 µs
• "1" to "0", max.	5 µs
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m

Analog inputs	
Number of analog inputs	2
integrated channels (AI)	2
Input ranges	
• Voltage	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
• Input resistance (0 to 10 V)	≥100k ohms
Cable length	
• shielded, max.	100 m; twisted and shielded

Analog outputs	
Number of analog outputs	2
integrated channels (AO)	2; 0 to 20 mA
Output ranges, current	
• 0 to 20 mA	Yes

Analog value generation	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	10 bit
• Integration time, parameterizable	Yes
• Conversion time (per channel)	625 µs

Encoder	
Connectable encoders	
• 2-wire sensor	Yes

1. Interface	
Interface type	PROFINET
Physics	Ethernet
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Functionality	

• PROFINET IO Controller	Yes
• PROFINET IO Device	Yes
• Open IE communication	Yes
• Web server	Yes
PROFINET IO Controller	
• Transmission rate, max.	100 Mbit/s
Services	
— Number of connectable IO Devices, max.	16
PROFINET IO Device	
Services	
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2
Protocols	
Supports protocol for PROFINET IO	Yes
PROFIBUS	Yes; CM 1243-5 required
AS-Interface	Yes
Protocols (Ethernet)	
• TCP/IP	Yes
Further protocols	
• MODBUS	Yes
Communication functions	
S7 communication	
• supported	Yes
• as server	Yes
• as client	Yes
Open IE communication	
• TCP/IP	Yes
• ISO-on-TCP (RFC1006)	Yes
• UDP	Yes
Web server	
• supported	Yes
• User-defined websites	Yes
Number of connections	
• overall	16; dynamically
Test commissioning functions	
Status/control	
• Status/control variable	Yes
• Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
Forcing	

• Forcing	Yes
Diagnostic buffer	
• present	Yes
Traces	
• Number of configurable Traces	2; Up to 512 KB of data per trace are possible

Integrated Functions	
Number of counters	6
Counting frequency (counter) max.	100 kHz
Frequency meter	Yes
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction interface	4; With integrated outputs
PID controller	Yes
Number of alarm inputs	4
Number of pulse outputs	4
Limit frequency (pulse)	100 kHz

Potential separation	
Potential separation digital inputs	
• Potential separation digital inputs	No
• between the channels, in groups of	1
Potential separation digital outputs	
• between the channels	No
• between the channels, in groups of	1

EMC	
Interference immunity against discharge of static electricity	
• Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes
— Test voltage at air discharge	8 kV
— Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
• Interference immunity on supply lines acc. to IEC 61000-4-4	Yes
• Interference immunity on signal cables acc. to IEC 61000-4-4	Yes
Interference immunity against voltage surge	
• on the supply lines acc. to IEC 61000-4-5	Yes
Interference immunity against conducted variable disturbance induced by high-frequency fields	
• Interference immunity against high-frequency radiation acc. to IEC 61000-4-6	Yes
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes; Group 1

- Limit class B, for use in residential areas

Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011

Degree and class of protection

Degree of protection acc. to EN 60529

- IP20

Yes

Standards, approvals, certificates

CE mark

Yes

UL approval

Yes

cULus

Yes

FM approval

Yes

RCM (formerly C-TICK)

Yes

Marine approval

- Marine approval

Yes

Ambient conditions

Free fall

- Drop height, max. (in packaging)

0.3 m; five times, in dispatch package

Ambient temperature during operation

- min.

-20 °C

- max.

60 °C; Number of simultaneously activated inputs or outputs 7 or 5 (no adjacent points) at 60 °C horizontal or 50 °C vertical, 14 or 10 at 55 °C horizontal or 45 °C vertical

- horizontal installation, min.

-20 °C

- horizontal installation, max.

60 °C

- vertical installation, min.

-20 °C

- vertical installation, max.

50 °C

Ambient temperature during storage/transportation

- min.

-40 °C

- max.

70 °C

Air pressure acc. to IEC 60068-2-13

- Storage/transport, min.

660 hPa

- Storage/transport, max.

1 080 hPa

- permissible operating height

-1000 to 2000 m

Relative humidity

- permissible range (without condensation) at 25 °C

95 %

Vibrations

- Vibrations

2G wall mounting, 1G DIN rail

- Operation, tested according to IEC 60068-2-6

Yes

Shock test

- tested according to IEC 60068-2-27

Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms

Extended ambient conditions

Pollutant concentrations	
— SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60% condensation-free
Configuration	
Configuration software	
• STEP 7	Yes
Programming	
Programming language	
— LAD	Yes
— FBD	Yes
— SCL	Yes
Cycle time monitoring	
• adjustable	Yes
Dimensions	
Width	130 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	500 g
last modified:	13.01.2016