SOLAHD

SVL Essential DIN Rail Series

SVL Series power supplies are perfect for high volume, controlled environment applications where essential features are the only requirement. When space inside an enclosure is at a premium, their small footprint makes these power supplies an excellent alternative to embedded open frame switchers. The DIN rail mounting capability provides quicker and easier installation while allowing for design flexibility. These power supplies range from 15 to 480 Watts in 5, 12, 24 and 48 Volt combinations.

Applications

- Test and Measure Equipment
- Scanners
- Instrumentation
- Printers Peripheral
- ATM Machines
- Semiconductor Fabrication Equipment
- Vending Machines

Features

- Universal Input
- Protection
 - Short Circuit
 - Over Voltage
 - Overload
 - Over Temperature
- Power Factor Correction
- Convection Cooling
- Blinking OCP Diagnostic
- DC OK LED
- DC OK Relay for >120 Watts models
- Two year limited warranty



Certifications and Compliances

All Models

- Cu Listed, Ind. Control Equipment, E61379
 - UL 508, CSA C22.2 No. 107.1
- c **W**_{US} Recognized Component, ITE, E137632 - UL 60950-1/CSA C22.2 No. 60950-1, 2nd Edition
- CE
 - IEC/EN60950-1, 2nd Edition
 - Model SVL 1-24-100, SVL 3-5-100, SVL 4-12-100, SVL 2-24-100 were evaluated for NEC Class 2 outputs
- RoHS Compliant

Related Products

- SDN-C Series
- SDN-P[™] Series
- SDP[™] Series





SVL Specifications <120W

Description	Catalog Number				
	SVL 3–5–100	SVL 1–24–100	SVL 6-5-100		
	Input				
nput Voltage Range		85-264 Vac			
- AC Range		100–240 Vac			
- DC Range ¹		120-375 Vdc			
- Frequency	50/60 Hz				
Nominal Current	0.5 A @ 115 Vac 0.3 A @ 230 Vac	0.8 A @ 115 Vac 0.4 A @ 230 Vac	0.9 A @ 115 Vac 0.5 A @ 230 Vac		
- Inrush Current max,	35 A @ 115 Vac 65 A @ 230 Vac	35 A @ 115 Vac 60 A @ 230 Vac			
fficiency	79% typ	88% typ	80% typ		
eakage Current	<1 mA @ 240 Vac				
Power Factor Correction	Meets EN61000-3-2 Class A				
		Output			
lominal Voltage	5 V	24 V	5 V		
- Tolerance		+/-2%			
/oltage Adjustable Range	5-5.5 V	24-28 V	5-5.5 V		
- Ripple (25 °C)		<75 mVp-p	1		
PARD (25 °C)		<75 mVp-p			
Nominal Current	3 A	1.25 A	6 A		
Max. Power	15 W	30	Ŵ		
loldup Time t full load (25 °C)	20 ms typ. @ 115 Vac 100 ms typ. @ 230 Vac				
Rise Time at full load (25 °C)	<100 ms				
itart Up at full load (25 °C)		<3000 ms @ 115 Vac, <1500 ms @ 230 Vac			
legulation		<0.5% Line and <1% Load			
		Environmental Data			
Operating Temperature	-20 °C to +70 °C				
Relative Humidity	5 to 95% RH Non-condensing				
Storage temp	-40 °C to +85 °C				
Power Derating ²		See derating tables.			
Shock	IEC60068-2-27: half sine wave 10 G, single axis for a duration of 11 ms operational and 50 G three axes for duration of 11 ms each non-operational				
Vibration		z at 2 g, 0.35 mm displacement, three axes for 60 .09 grms, three axes for 20 min each non-operation			
		Protections			
Overvoltage Protection	6.3-7.4 V, Latching	30-34.8 V, Latching	6.3-7.4 V, Latching		
Overload Protection	Hiccup				
Over Temperature Protection	No component damage, latch mode				
Short Circuit	Hiccup mode, non-latching (auto-recovery when the fault is removed)				
		Reliability			
MTBF	>350 khrs (115 Vac/230 Vac @ 25 °C) acc. to Telcordia SR-332 issue 3				
		EMC			
Galvanic Isolation	I/P to C)/P: 3 K Vac; I/P to GND: 1.5 K Vac; O/P to GND:	0.5 K Vac		
Emissions	EN55022 (CISPR22) Class B, EN55011 Class B, EN61000-6-3, EN61000-6-4, EN61000-3-3, EN61204-3, EN61000-3-2 Class A				
mmunity	EN55024, EN61000-6-1, EN61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11, 12) Level 3, Performance Criteria A				
		General			
lousing		Plastic			
l x W x D in (mm)svl	2.95 x 0.82 x 3.52 (75.0 x 21.0 x 89.5)		2.95 x 1.18 x 3.52 (75.0 x 30.0 x 89.5)		
Jnit Weight	0.242 lb (110 g)		0.368 lb (167 g)		
Shipping Weight	0.309 lb (140 g) 0.419 lb (190 g)				
	GREEN light = DC OK , OCP = blinking				
LED Signals	No				
DC OK Relay Contact					
Warranty	2 year ety file it is only to confirm product functional performance.				



SOLAHD

SVL Specifications 120W and Above

Description	Catalog Number					
	SVL 4–12–100	SVL 2–24–100	SVL 4–24–100			
	Input					
Input Voltage Range		85-264 Vac				
- AC Range		100–240 Vac				
– DC Range ¹	120-375 Vdc					
– Frequency	50/60 Hz					
Nominal Current	1.0 A @ 115 Vac 0.6 A @ 230 Vac	1.0 A @ 115 Vac 0.6 A @ 230 Vac	1.2 A @ 115 Vac 0.6 A @ 230 Vac			
1	0.0776 200 440	35 A @ 115 Vac	0.071@200 Vac			
– Inrush Current max.	60 A @ 230 Vac					
Efficiency	88% typ 89% typ					
Leakage Current		<1 mA @ 240 Vac				
Power Factor Correction	Meets EN	Meets EN61000-3-2 Class A Active PFC >0.9				
		Output				
Nominal Voltage	12 V		24 V			
– Tolerance	10.15.1/	+/-2%	04.00.1/			
Voltage Adjustable Range	12-15 V		24-28 V			
– Ripple (25 °C)	<75 mVp-p					
PARD (25 °C)	4 A	<75 mVp-p 2.1 A	4 A			
Nominal Current Max. Power	48 W	50 W	96 W			
Max. Power Holdup Time		styp. @ 115 Vac	25 ms typ. @ 115 Vac			
at full load (25 °C)		s typ. @ 230 Vac	50 ms typ. @ 230 Vac			
Rise Time at full load (25 °C)	<100 ms					
Start Up at full load (25 °C)		<3000 ms @ 115 Vac, <1500 ms @ 230 Va	ac			
Regulation		<0.5% Line and <1% Load				
		Environmental Data				
Operating Temperature	-20 °C to +70 °C					
Relative Humidity		5 to 95% RH Non-condensing				
Storage temp		-40 °C to +85 °C				
Power Derating ²		See SVL derating tables.				
Shock	IEC60068-2-27: half sine wa	ve 10 G, single axis for a duration of 11 ms operat of 11 ms each non-operational	ional and 50 G three axes for duration			
Vibration	IEC60068-2-6: 10 Hz to 500 Hz	at 2 g, 0.35mm displacement, three axes for 60 m 2.09 grms, three axes for 20 min each non-oper				
		Protections				
Overvoltage Protection	16-18.7 V, Latching	30-34	.8 V, Latching			
Overload Protection		Current foldforward and then hiccup				
Over Temperature Protection		No component damage, latch mode				
Short Circuit	Hicou	up mode, non-latching (auto-recovery when the fa	ult is removed)			
		Reliability				
MTBF	>350 khrs (115 Vac/230 Vac @ 25 °C) as per Telcordia SR-33	32 issue 3 Jan 2011.			
		EMC				
Galvanic Isolation	I/P t	o O/P: 3 K Vac; I/P to GND: 1.5 K Vac; O/P to GN	ID: 0.5 K Vac			
Emissions	EN55022 (CISPR22) Class B, EN55011 Class B, EN61000-6-3, EN61000-6-4, EN61000-3-3, EN61204-3, EN61000-3-2 Class A					
Immunity	EN55024, EN61000-6-1	, EN61000-6-2 (EN61000-4-2, 3, 4, 5, 6, 8, 11, 1	2) Level 3, Performance Criteria A			
		General				
Housing		Plastic				
H x W x D in (mm)	2.95 x 1.18 x 3.52 (75.0 x 30.0 x 89.5)		2.95 x 1.77 x 3.93 (75.0 x 45.0 x 100.0)			
Unit Weight	0.390 lb (177 g)		0.698 lb (317 g)			
Shipping Weight	0.478 lb (217 g) 0.816 lb (370 g)					
LED Signals	GREEN light = DC OK , OCP = blinking					
DC OK Relay Contact	No					
Warranty	2 year					

Visit our website at **www.emerson.com** or contact Technical Services at **(800) 377-4384** with any questions. © September 2017



SVL Specifications 120W and Above

SVL 2-48-100	SVL 5-24-100	SVL 10-24-100	SVL 20-24-100	
	Innut			
	Input			
	85-264 Vac			
	100–240 Vac			
120-375 Vdc				
	50/60 Hz			
	-	2.8 A @ 115 Vac 1.4 A @ 230 Vac	5.4 A @ 115 Vac 2.7 A @ 230 Vac	
	20 A typ.@ 115 Vac 40 A typ.@ 230 Vac		40A typ.@ 115 Vac 80A typ.@ 230 Vac	
88% typ				
	<1 mA @ 240 Vac	;		
Meets EN61000-3-2	2 Class A	Active PFC >0.95		
	Output			
48V		24V		
· · ·	+/-2%			
44-56 V		22-28 V		
<120 mVp-p		<100 mVp-p		
<150 mVp-p		<120 mVp-p		
2.5 A	5 A	10 A	20 A	
120 W		240 W	480 W	
10 ms typ.@ 115 Vac				
		230 Vac		
	· · · · · ·			
·				
·				
of 11 ms each non-operational				
IEC60068-2-6: sine wave; 10 Hz to 500 Hz at 2 g, 0.35 mm displacement, three axes for 60 min each operational and 5 Hz to 500 Hz at 2.09 grms, three axes for 20 min each non-operational				
	Protections			
, 0, 1				
			N	
		1 1 2	<u>,</u>	
		,		
>700 kbrs (11	•	cordia SB-332 issue 3 Jan 2011		
	, ,			
/D +		: O/P to GND: 0.5 K Vac		
LINO 1000-0-1, LINO 1000-0			CLIVIT TI W ZUU Vau	
	4.63	4.87 x 2.36 x 4.63	4.87 x 3.37 x 5.06	
			(123.6 x 85.5 x 128.	
			2.87 lb (1300 g)	
1.46 lb (660 g	o,		3.20 lb (1452 g)	
Yes 2 year				
	1.40 A @ 230 Meets EN61000-3-: Meets EN61000-3-: 48V 48V 48V 44-56 V <120 mVp-p <150 mVp-p 2.5 A 120 W 120 W	2.20 A @ 115 Vac 1.40 A @ 230 Vac 20 A typ.@ 115 Vac 40 A typ.@ 230 Vac 88% typ <1 mA @ 240 Vac	2:20 A @ 115 Vac 2:8 A @ 115 Vac 1:40 A @ 230 Vac 20 A typ, @ 115 Vac 40 A typ, @ 230 Vac 88% typ 1:1 mA @ 240 Vac 88% typ 1:1 mA @ 240 Vac Meets EN61000-3:2 Class A Active PFC Output 0utput 48V 2:4 V 44:56 V 2:2.28 V <1:00 mVp-p	

1. DC input range is not listed in safety file it is only to confirm product functional performance.




SOLAHD


230


264

SVL Derating Tables





120 Watt and 480 Watt Models





SVL Series Dimensions





Catalog	Dimensions – inches (mm)			
Number	Н	w	D	
SVL 3-5-100	2.95 (75.0)	0.82 (21.0)	3.52 (89.5)	
SVL 1-24-100	2.95 (75.0)	0.82 (21.0)	3.52 (89.5)	
SVL 6-5-100	2.95 (75.0)	1.18 (30.0)	3.52 (89.5)	
SVL 4-12-100	2.95 (75.0)	1.18 (30.0)	3.52 (89.5)	
SVL 2-24-100	2.95 (75.0)	1.18 (30.0)	3.52 (89.5)	
SVL 4-24-100	2.95 (75.0)	1.77 (45.0)	3.93 (100.0)	
SVL 2-48-100	4.84 (123.6)	1.57 (40.0)	4.63 (117.6)	
SVL 5-24-100	4.84 (123.6)	1.57 (40.0)	4.63 (117.6)	
SVL 10-24-100	4.87 (123.6)	2.36 (60.0)	4.63 (117.6)	
SVL 20-24-100	4.87 (123.6)	3.37 (85.5)	5.06 (128.5)	

