

SIMATIC S7-1200, DIGITAL INPUT SM 1221, 8DI, 24V DC, SINK/SOURCE INPUT



Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> <li>• 24 V DC</li> </ul>	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	105 mA
Digital inputs	
<ul style="list-style-type: none"> <li>• from load voltage L+ (without load), max.</li> </ul>	4 mA; per channel
Output voltage	
Power supply to the transmitters	
<ul style="list-style-type: none"> <li>• present</li> </ul>	Yes
Power loss	
Power loss, typ.	1.5 W
Digital inputs	
Number of digital inputs	8
<ul style="list-style-type: none"> <li>• in groups of</li> </ul>	2

Input characteristic curve in accordance with IEC 61131, type 1	Yes
<b>Number of simultaneously controllable inputs</b>	
all mounting positions	
— up to 40 °C, max.	8
horizontal installation	
— up to 40 °C, max.	8
— up to 50 °C, max.	8
vertical installation	
— up to 40 °C, max.	8
<b>Input voltage</b>	
• Type of input voltage	DC
• Rated value (DC)	24 V
• for signal "0"	5 V DC at 1 mA
• for signal "1"	15 VDC at 2.5 mA
<b>Input current</b>	
• for signal "0", max. (permissible quiescent current)	1 mA
• for signal "1", min.	2.5 mA
• for signal "1", typ.	4 mA
<b>Input delay (for rated value of input voltage)</b>	
for standard inputs	
— parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
for interrupt inputs	
— parameterizable	Yes
<b>Cable length</b>	
• shielded, max.	500 m
• unshielded, max.	300 m
<b>Interrupts/diagnostics/status information</b>	
Alarms	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
• for maintenance	Yes
• Status indicator digital input (green)	Yes
<b>Potential separation</b>	
Potential separation digital inputs	
• between the channels, in groups of	2
<b>Degree and class of protection</b>	

Degree of protection acc. to EN 60529	
• IP20	Yes
<b>Standards, approvals, certificates</b>	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
<b>Ambient conditions</b>	
<b>Free fall</b>	
• Fall height, max.	0.3 m; five times, in dispatch package
<b>Ambient temperature during operation</b>	
• permissible temperature range	-20 °C to +60 °C horizontal mounting, -20 °C to 50 °C vertical mounting, 95% humidity, non-condensing
• min.	-20 °C
• max.	60 °C
• permissible temperature change	5°C to 55°C, 3°C / minute
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Air pressure acc. to IEC 60068-2-13</b>	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
<b>Relative humidity</b>	
• permissible range (without condensation) at 25 °C	95 %
<b>Connection method</b>	
required front connector	Yes
<b>Mechanics/material</b>	
<b>Enclosure material (front)</b>	
• Plastic	Yes
<b>Dimensions</b>	
Width	45 mm
Height	100 mm
Depth	75 mm
<b>Weights</b>	
Weight, approx.	170 g
<b>last modified:</b>	08.01.2016