

OneTouch Silencer

OC-09-530-QO



More Information



[Spec Sheet](#)



[UL Recognized](#)



RoHS Compliant

Specifications


Revision: 3.18

Medium Loud Continuous w/ Mute; Rate; Panel Mount Case and Quick Connect Blades Termination

Mounting:	Panel Mount
Operating Mode:	Medium Loud Continuous w/ Mute
Operating Voltage:	5-30 Vdc
Operating Frequency:	
Typical Operating Current:	15 mA at 5 Vdc 20 mA at 30 Vdc
Typical Sound Pressure:	97±5 dB(A), at 5 Vdc, at 24 inches (61 cm), at 25°C 97±5 dB(A), at 30 Vdc, at 24 inches (61 cm), at 25°C
Termination:	Quick Connect Blades
Termination Strength:	Pull test with a maximum of 22 pounds (10 kg) load
Operating Temperature:	-20_C to +65_C
Storage Temperature:	-40_C to +85_C
Surge Voltage:	20% over maximum rated voltage for less than 5 minutes
Reverse Voltage Protection:	To the maximum operating voltage
Construction Materials:	Internal Circuit- Audio-oscillator and piezoelectric driver Potting- 2 parts epoxy resin or silicone, black Diaphragm- Stainless Steel 304
Gasket:	
Environmental Durability:	ASTM B117 Certified - Withstands exposure to salt spray for 300 hours IP 68 Certified - Withstands water submergence and dust exposure Humidity- 95% relative humidity at +40_C continuously for 100 hours. Vibration- Withstands vibration between 0 and 55 Hz. on all axes.
Life Expectancy:	10 years under normal operating conditions.
Warranty:	For a period of two years from the date of manufacture under normal operating conditions.
View Terms and Conditions of Sale	


Dimensions

REAR




TOLERANCES ARE: ± 0.03 in.
[± 0.76 mm]

SIDE




RING



1125-24 UNF THREADS
FOR REFERENCE ONLY

FRONT



PANEL MOUNTING



FITS PANELS UP TO
0.25 in (6.35 mm) THICK

"Q" TERMINALS

