

Datasheet

RS Pro Stainless Steel Liquid Sensor/Switch without Indicator, 0.5 to 15 L/min, 4.5 to 24 V dc

RS Stock No: 511-3971



Product Details

RS Pro stainless steel liquid sensor/switch without indicator, has a maximum pulse rate of 0.5 to 15 L/min. It takes 4.5 to 24 V dc supply voltage and offers excellent performance for a wide range of process fluids.

Features and Benefits

- Suitable for a wide range of process fluids
- Excellent performance
- Traceable calibration certificate



ENGLISH

Specifications:

| | |
|-------------------------------|---------------------------------|
| Connection Type | 1/2 BSP |
| Device Type | Sensor/Switch without Indicator |
| Material | Stainless Steel |
| Maximum Flow Rate | 15 L/min |
| Maximum Operating Temperature | +125°C |
| Maximum Pressure | 10 bar |
| Media Monitored | Liquid |
| Minimum Flow Rate | 0.5 L/min |
| Minimum Operating Temperature | -25°C |
| Pipe Diameter Range | 1/2 in |
| Supply Voltage | 4.5 to 24 V dc |