

Ultra

UB-09-628-Q(S)



More Information


Beep Tone

 [Spec Sheet](#)

 [UL Recognized](#)

 RoHS Compliant

OUTPUT SOUND and CURRENT CONSUMPTION vs. INPUT VOLTAGE PERFORMANCE.



Specifications

Revision: 3.18

Ultra Loud Beep Tone; Slow Rate; Panel Mount Case and Quick Connect Blades Termination

Mounting:	Panel Mount
Operating Mode:	Ultra Loud Slow Beep Tone
Operating Voltage:	6-28 Vdc
Operating Frequency:	
Typical Operating Current:	20 mA at 6 Vdc 50 mA at 28 Vdc
Typical Sound Pressure:	93±5 dB(A), at 6 Vdc, at 24 inches (61 cm), at 25°C 109±5 dB(A), at 28 Vdc, at 24 inches (61 cm), at 25°C
Termination:	Quick Connect Blades
Termination Strength:	Pull test with a maximum of 22 pounds (10 kg) load
Operating Temperature:	-20_C to +65_C
Storage Temperature:	-40_C to +85_C
Surge Voltage:	20% over maximum rated voltage for less than 5 minutes
Reverse Voltage Protection:	To the maximum operating voltage
Construction Materials:	Internal Circuit- Audio-oscillator and piezoelectric driver Potting- 2 parts epoxy resin or silicone, black Diaphragm- Stainless Steel 304

Gasket:

Environmental Durability: ASTM B117 Certified - Withstands exposure to salt spray for 300 hours
IP 68 Certified - Withstands water submergence and dust exposure
Humidity- 95% relative humidity at +40_C continuously for 100 hours.
Vibration- Withstands vibration between 0 and 55 Hz. on all axes.

Life Expectancy:

10 years under normal operating conditions.


Warranty:

For a period of two years from the date of manufacture under normal operating conditions.

[View Terms and Conditions of Sale](#)


Dimensions

REAR




TOLERANCES ARE: ± 0.03 in.
[± 0.76 mm]

SIDE




RING



1.125-24 UNF THREADS
FOR REFERENCE ONLY

FRONT



PANEL MOUNTING



FITS PANELS UP TO
0.25 in [6.35mm] THICK

"Q" TERMINALS

