



Datasheet

Twin IP68 Guarded Foot Switch

RS Stock No. 116-798



Degree of protection	IP68
Materials of Construction	Cast Aluminium body with heavy gauge rolled steel guard
Colour	Black body, silver treadle & Alert Orange guard
Cable Connection	Single M20 entry
Contact Action	SPDT Momentary each side
Electrical Rating	16A 125-250V a.c. 0.375kW 125-250V a.c. 250V a.c. max
Features & Benefits	Divider bar between treadles reduces accidental operation of both units. 4 holes for mounting on floor or equipment. Non skid base pad. Guard covers entire foot switch
Weight	4.5kg
Size	(See below)

