

ENGLISH

Datasheet

RS Pro Test Lead Wire Single Core 60m

RS Stock No: 714-1732



Product Details

RS Pro single core test lead wire of 60 m, is a 80/20 nickel chrome alloy resistance wire, suitable for control resistors. It has operating temperatures of up to 1150 °C.

Features and Benefits

- 80/20 nickel chrome alloy resistance wire
- Operating temperatures of +1150°C
- Suitable for control resistors
- 200 g reels





Specifications:

Cable Shape
Conductor Material
Nickel Chrome Alloy
Length
60 m
Maximum Operating Temperature
Operating Temperature Range
Maximum of +1150°C
Outer Diameter

Single Core
Nickel Chrome Alloy
Maximum Alloy
00 m
Maximum Operating Temperature
00 m
Maximum of +1150°C
00 m
Maximum of +1150°C

80/20 Nickel Chrome			
Size	Dia mm	Resistance	Metres/Kg
		at 20 deg C	
		ohm/m	
14swg	2.032	0.33270	36.89
16swg	1.626	0.51883	57.53
18swg	1.220	0.92388	102.40
20swg	0.913	1.64240	182.10
22swg	0.711	2.71250	300.80
24swg	0.559	4.40060	488.00
25swg	0.508	5.32850	590.90
29swg	0.345	11.48600	1274.00
35swg	0.213	30.30900	3361.00