Twin Low Profile Foot Switch



Degree of protection IP20

Materials of Construction Sheet steel.

Colour Black.

Cable Connection 2.5M of 16/4 cable no plug

Contact Action SPDT Momentary wired N/O on each side

Electrical Rating 13A 125-250V a.c. 0.375kW 125-250V a.c.

Features & Benefits Divider bar between treadles reduces accidental operation of both units.

2 holes for mounting on floor or equipment.

Non skid base pad.

Weight 1.8kg

Size (See below)





