

# LED Landscape Replacement Lamps



G4

G9

- 2.5 watts
- 25,000 hours\*
- G4/G9 base
- 200° beam spread

## features

- Direct replacement for halogen Incandescent G4 and G9 base lamps
- Consumes 75% less energy and lasts 25x longer than incandescent bulbs
- 25,000 hour rated life for ENERGY STAR® Approved lamps\*
- 50,000 hour design life\*\*
- Choice of 3000K, 4000K, and 5000K color temperatures
- 200° multi-directional beam angle
- Integrated driver
- Contains no mercury; RoHS compliant
- Emits virtually no UV or IR radiation



## performance

- G4 12V 2.5W 200 LM replaces 10W halogen Incandescent
- G9 120V 2.5W 200 LM replaces 10W halogen Incandescent
- 80+ CRI
- Non-dimmable
- Not for use in totally enclosed luminaires
- Operating Temperature: -40°F to 104°F (-40°C to 40°C)

## applications

- Landscape lighting
- Deck and patio
- Accent lighting
- Under cabinet lighting
- Pendant and downlighting
- Signs and display lighting
- Steps / Pathway


\* Early initial qualification for ENERGY STAR allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass ENERGY STAR requirements, manufacturers may increase the lifetime of a product as dictated by ENERGY STAR guidelines. See [http://www.energystar.gov/index.cfm?fuseaction=products\\_for\\_partners.showLightbulbs](http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs) for further details.

\*\* Design life is based on engineering testing and probability analysis



# LED Landscape Replacement Lamps

## dimensions



## ordering information

Order Code	Litespan Part #	Watts	Volts	Lumens	CCT	CRI	MOL	Life Hours*	Replaces Incandescent
G4 Landscape Replacement 12VAC									
<b>08605</b>	<b>LED2WG4/830K-G4</b>	3W	12V	200	3000K	80+	1.59"	25,000	10W G4
<b>08606</b>	<b>LED2WG4/840K-G4</b>	3W	12V	200	4000K	80+	1.59"	25,000	10W G4
<b>08607</b>	<b>LED2WG4/850K-G4</b>	3W	12V	200	5000K	80+	1.59"	25,000	10W G4
G9 Landscape Replacement 120V									
<b>08608</b>	<b>LED2WG9/830K-G4</b>	3W	120V	200	3000K	80+	1.96"	25,000	10W G9
<b>08609</b>	<b>LED2WG9/840K-G4</b>	3W	120V	200	4000K	80+	1.96"	25,000	10W G9
<b>08610</b>	<b>LED2WG9/850K-G4</b>	3W	120V	200	5000K	80+	1.96"	25,000	10W G9

\* 25,000 hour ENERGY STAR® rated life. 50,000 hour design life. See note on obverse.

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335

