



TEL (915) 590-8500
FAX (915) 590-8510

SIEMENS

Cat. No. HF362SSW **Fusible Heavy Duty Safety Switch** **Type VB II**
60 Amps Maximum **600 Volts AC(V~)Maximum** **600¹¹ Volts DC(V-)-Maximum**
Type 4/4X **Watertight 316 Stainless Steel**

Horsepower Ratings	240 VAC ¹ 1Ø	240 VAC 3Ø	480 VAC ¹ 1Ø	480 VAC 3Ø	600 VAC ¹ 1Ø	600 VAC 3Ø	250 VDC ¹	600 ¹¹ VDC ¹
Std. HP (Std. Fuse) ⁴	3	7½	5	15	10	15	10	25
Max. HP (Time Delay)	10	15	20	30	25	50	—	30

Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.
Horsepower ratings listed above are suitable for use with High Efficiency motors.
Suitable for use as Service Equipment when used with factory installed ground bar on 3 phase, 3 wire systems or when used with **HN623** neutral kit on 1 phase, 3 wire or 3 phase, 4 wire systems.

Fuse and Short Circuit Information
When used with Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 600 volts maximum, this switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 600 volts, maximum.
When used with Class R fuses and Class R fuse clip kit **HR62** properly installed, this switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, 600 volts maximum.
When used with Class J fuses with the load base relocated to the "J Fuse" position marked on the enclosure this switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, 600 volts maximum.
Danger – Unless class R or J fuses are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.
When used with fuses marked with DC ratings, this switch is suitable for use on a circuit capable of delivering not more than the DC interrupting rating marked on the fuse, up to a maximum of 10,000 amperes, 600¹¹ volts DC.
Danger – Unless fuses marked for an interrupting rating of 10,000 amperes at 600¹¹ volts DC are used, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

Renewable link fuses are not recommended

Hazardous voltage.
Will cause death or serious injury.

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

Terminal & Wire Information USE 60°C / 75°C COPPER OR ALUMINUM WIRE

Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	14-2 AWG	35 lb-ins, 14-10 AWG / 40 lb-ins, 8 AWG 45 lb-ins, 6-4 AWG / 50 lb-ins, 3-2 AWG	80 lb-ins.
Service Ground	14-4 AWG	35 lb-ins, 14-10 AWG / 40 lb-ins, 8 AWG 45 lb-ins, 6-4 AWG	24 lb-ins.

UL Listed Compression Lugs (Refer to manufacturers instructions for proper installation)⁶

Wire Size (AWG OR kcmil)	Burdny		Thomas & Betts		IlSCO	
	Cu Only	Cu / Al	Cu Only	Cu / Al	Cu Only	Cu / Al
14-10			256-30695-1352	60097		
8	YA8C-L1 Box YA8C-TC14	YA8CA3	54130 54930BE	60102 61102		ACL - 8
6	YA6C-L Box YA6C	YA6CA1	54105 54905BE	60107 61107	CRB-6 CRB-6L	ACL - 6
4			54106	61112	CRB-4	

Inspection record number:

Accessories	HA161234	Neutral	HN623	Class R Fuse Kit (Rejects Class H & K Fuses)	HR62
Aux. Switch (1NO - 1NC)	HA161234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234	Wire Grip Kit (CU)	HLC612
Aux. Switch (2NO - 2NC)	HA261234	Isolated Ground Lug Kit	HG261234	Hub Kits	SSH075 (3/4") SSH100 (1") SSH125 (1 1/4")
Low Voltage Aux. Sw. (1NO - 1NC)	HA361234	Fuse Puller (3 per kit)	HP62		
Compression Lug Neutral Barrier Kit	HCL623				

Replacement Parts

Line Base	HFB62	Wire Grip Kit (AL)	HL612	Handle / Handle Guard	HH6123SS
Load Base	HBB62	Mechanism	HM6123S	Door	HF362SSWDOOR

Protected by one or more of the following US Patents: 5,914,460, 6,134,979, 6,356,460, 5,945,650, 5,990,439.

¹ Use outer two poles.
⁴ The starting current of motors more than the standard horsepower or kilowatt ratings may require the use of fuses with appropriate time delay characteristics.
⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.
⁶ If compression lugs are used for the neutral, order compression lug neutral barrier kit **HCL623**.
¹¹ 600 VDC ratings apply when wired per cover wiring diagram.

For questions on this device please call 1-800-241-4453 Siemens Industry, Inc. Norcross, GA 30092 USA Pc. No. 502148F01 1111
<http://www.usa.siemens.com/powerdistribution>
Assembled in Mexico

COMPANY NAME			JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.					
Siemens Industry, Inc								
THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.	MATERIAL		SIZE		<input type="checkbox"/> OK TO PRINT AS IS <input type="checkbox"/> MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF		PART NO. 502148F01	
	Synthetic Paper		WIDTH		<input type="checkbox"/> OK TO PRINT WITH CORRECTIONS AS MARKED		DESCRIPTION: Label	
	Lamination: No		4.63"		AUTHORIZED BY		DATE	
	INK COLORS		8.5"		REVISION LEVEL 38P		DESIGNER	
BLACK 185 RED		ROUND CORNER RADIUS		DATE		Gibran Camacho		
		.125"		DATE		11/23/11		