



WIRING DIAGRAM	LOCKNUT LN-M18	SPECIFICATIONS																
<p>OUTPUT: AZ3X</p> <p>WARNING: NO SHORT-CIRCUIT PROTECTION. ALWAYS WIRE A LOAD IN SERIES WITH THE SENSOR.</p>	<p>M18x1</p> <p>1.083 27.5</p> <p>.945 24.0</p> <p>.157 4.0</p>	<table><tr><td>RATED OPERATING DISTANCE</td><td>10mm = .394"</td></tr><tr><td>MOUNTING MODE</td><td>NON-FLUSH</td></tr><tr><td>TEMPERATURE DRIFT</td><td>≤±10%</td></tr><tr><td>HYSTERESIS</td><td>3-15%</td></tr><tr><td>MIN. REPEAT ACCURACY</td><td>≤ 2%</td></tr><tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (+13°F to +158°F)</td></tr><tr><td>RATED OPERATIONAL VOLTAGE (VAC/VDC)</td><td>20-250 VAC/10-300 VDC</td></tr><tr><td>RESIDUAL RIPPLE</td><td>≤ 10%</td></tr></table>	RATED OPERATING DISTANCE	10mm = .394"	MOUNTING MODE	NON-FLUSH	TEMPERATURE DRIFT	≤±10%	HYSTERESIS	3-15%	MIN. REPEAT ACCURACY	≤ 2%	OPERATING TEMPERATURE	-25°C to +70°C (+13°F to +158°F)	RATED OPERATIONAL VOLTAGE (VAC/VDC)	20-250 VAC/10-300 VDC	RESIDUAL RIPPLE	≤ 10%
RATED OPERATING DISTANCE	10mm = .394"																	
MOUNTING MODE	NON-FLUSH																	
TEMPERATURE DRIFT	≤±10%																	
HYSTERESIS	3-15%																	
MIN. REPEAT ACCURACY	≤ 2%																	
OPERATING TEMPERATURE	-25°C to +70°C (+13°F to +158°F)																	
RATED OPERATIONAL VOLTAGE (VAC/VDC)	20-250 VAC/10-300 VDC																	
RESIDUAL RIPPLE	≤ 10%																	



SOURCE DRAWING - FOR REFERENCE ONLY

<div>RELATED DOCUMENTS</div> <div>1. 2. 3. 4.</div>					<div>3RD ANGLE PROJECTION</div> <div></div>		<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div>		<div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div> <div><b>TURCK INC</b> High Technology Sensors and Automation Controls</div>				
					<div>MATERIAL</div> <div>SEE NOTES</div>		<div>DRFT</div> <div>RDS</div>		<div>DATE</div> <div>02/17/11</div>		<div>DESCRIPTION</div> <div>NI10-G18-AZ3X 10M</div>		
							<div>DSGN</div>		<div>SCALE</div> <div>1 = 1.0</div>				
					<div>FINISH</div>		<div>ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY</div> <div>CONTACT TURCK FOR MORE INFORMATION</div>		<div>UNIT OF MEASUREMENT</div> <div>INCH [ MILLIMETER ]</div> <div>DO NOT SCALE THIS DRAWING</div>		<div>IDENTIFICATION NO.</div> <div>T4330590</div>		<div>REV</div> <div>A</div>
<div>FILE: T4330590</div>		<div>SHEET 1 OF 1</div>											
<div>A</div>	<div>DRAWING RELEASE</div>			<div>RDS</div>	<div>02/17/11</div>								
<div>REV</div>	<div>DESCRIPTION</div>			<div>BY</div>	<div>DATE</div>		<div>ECO NO.</div>						