

Datasheet

RS Pro Stainless Steel Masonry Fixing M10, fixing hole diameter 10mm, length 125mm

RS Stock No: **622-1972**



Product Details

RS Pro masonry fixing captive stud bolt anchor is made of A4-316 grade stainless steel for corrosion resistance. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm². The anchor measures 125 mm long with M10 threading that is suitable for 10 mm fixing hole diameter.

Features and Benefits

- Captive Stud Through Bolt Anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm²
- 10 mm fixing hole diameter
- 125 mm long



ENGLISH

Specifications:

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	10 mm
Length	125 mm
Maximum Fixing Thickness	50 mm
Thread Size	M10
Grade	316 (A4)
Minimum Hole Depth	70 mm