



ENGLISH

Datasheet

## **RS Pro Nitrile Rubber Flexible Tube, Black, 12mm External Diameter, 50m Long, Compressed Air Applications**

RS Stock No: **340-0576**



### **Product Details**

RS Pro nitrile rubber flexible tube is 50 m long and has an external diameter of 12 mm. This tube in black colour, is suitable for compressed air applications.

### **Features and Benefits**

- Excellent resistance to aliphatic based hydrocarbon fluids
- Low gas permeation
- Good resistance to aromatic solvents and alcohols
- High tear and abrasion resistance
- Intended for non-pressure applications



ENGLISH

### Specifications:

Bend Radius	33 mm
Colour	Black
Inner Diameter	8 mm
Length	50 m
Material	Nitrile Rubber
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-20°C
Operating Temperature Range	-20 to +100°C
Outer Diameter	12 mm
Reinforced	No
Suitable Applications	Compressed Air