
FEMALE END VIEW	MALE END VIEW
1 0 3	3 0 0 1
1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK	1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK
O pico iost.	Pico Fast,

SPECIFICATIONS							
NYLON OR TPU							
TPU/YELLOW							
BRASS/GOLD							
BRASS/NICKEL							
2.0 A							
125 VAC/VDC							
TPU/BLACK							
PVC							
4x26 AWG							
-40°C to +90°C (-40°F to +194°F)							
MEETS NEMA 1,3,4,6P AND IEC IP67							



CABLE LENGTH	TOLERANCE * + 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER							
ALL LENGTHS								
STRIP LENGTH	TOLERANCE *							
0-7mm	±0.5mm ±1.0mm ±2.0mm							
8-29mm								
30-49mm								
50-69mm	±3.0mm							
70-100mm	±4.0mm							
OVER 100mm	±5.0mm							
* UNILESS OTHERWISE SPECIFIED								

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

	SPECIFIC LENGTHS.	(CIC I	IO ONDEN		MATERIAL		DRFT	RWC	DATE 10/08/07	DESCRIPTION	,	
2. "/S90" DESIGNATES THERMOPLASTIC POLYURETHANE (TPU) CABLE.			SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY CONTACT TURCK	APVD		SCALE 1=1.0	PKG 4M-*-PSG 4M/	4M/S90			
					FINISH			ASUREMENT	IDENTIFICATION NO.		REV	
F	UPDATE MALE COUPLING NUT PER ECO	KMY	05/09/13	40191	SEE SPECIFICATIONS	FOR MORE INFORMATION						
REV	DESCRIPTION	BY	DATE	ECO NO.			DC	NOT SCALE	THIS DRAWING	FILE: 777001825	SHEET	1 OF 1

RELATED DOCUMENTS

2.

3.

3RD ANGLE PROJECTION

THIS DRAWING IS
CONFIDENTIAL AND THE
PROPERTY OF TURCK
INC. USE OF THIS
DOCUMENT WITHOUT
WRITTEN PERMISSION IS
PROHIBITED.

SOURCE DRAWING - FOR REFERENCE ONLY

Turck iac

High Technology Sensors and Automation Controls

3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769

(763) 553-7300

turck.com

(763) 553-0708 fax