

Datasheet

RS Pro Stainless Steel Liquid Sensor/Switch without Indicator, 0.25 to 6.5 L/min, 4.5 to 24 V dc

RS Stock No: 511-3965



Product Details

RS Pro stainless steel liquid sensor/switch without indicator, has a maximum pulse rate of 0.25 to 6.5 L/min. It takes 4.5 to 24 V dc supply voltage and offers excellent performance for a wide range of process fluids.

Features and Benefits

- Suitable for a wide range of process fluids
- Excellent performance
- Traceable calibration certificate

**Specifications:**

Connection Type	1/4 BSP
Device Type	Sensor/Switch without Indicator
Material	Stainless Steel
Maximum Flow Rate	6.5 L/min
Maximum Operating Temperature	+150°C
Maximum Pressure	10 bar
Media Monitored	Liquid
Minimum Flow Rate	0.25 L/min
Minimum Operating Temperature	-40°C
Pipe Diameter Range	1/4 in
Supply Voltage	4.5 to 24 V dc