





SL-20XP® LED RECHARGEABLE FLASHLIGHT

FL1 STANDARD	HALOGEN	3 LEDs
	120 LUMENS	20 LUMENS
	1h 30min	11h 30min
	253m	28m
	16,000cd	200cd



As a result of severe storms (summer or winter), it's wise to plan for emergencies resulting in a major power loss as a result of extremes in hot or cold weather, hurricanes, typhoons, thunder storms, blizzards, and ice storms. Under severe weather conditions like these, portable systems offer an advantage when it becomes necessary to move about a facility to power down or disconnect critical equipment, retrieve sensitive documents, or guide employees through remote areas that lack adequate backup lighting.

The solution is Streamlight's line of rechargeable, portable lanterns and flashlights that are equipped with "smart" power failure circuitry. When the power goes out, these rugged, dependable workhorse lighting tools switch on, helping to light the way to safety in pitch dark conditions. Ideal for evacuation team leaders and for placement in planned evacuation routes/areas, stairways and hallways.

Material/Lens Lightweight, super-tough nylon polymer case designed with non-slip rubber comfort grip with an unbreakable polycarbonate lens with scratch-resistant coating

Dims/Weight Length: 13.2 in. (33.53 cm) Major Diameter: 2.50 in. (6.35 cm); Body Diameter: 1.50 in. (3.81 cm); 1.1 lbs (0.41 Kg)* - *With battery

Light Source/ Output 8-watt, 6-volt Halogen Bulb with 100 hour lifetime; 3 High Intensity LEDs with 100,000 hour Lifetime
Halogen - 120 lumens; 253m beam distance; 16,000 candela; runs 1.5 hours
LEDs - 20 lumens; 200 candela; 28m beam; runs 11.5 hours

Switch Lifetime dual switch control for halogen and LEDs. Momentary and constant on for Halogen Constant on for LEDs

Battery 5-cell, 6.0V NiCd or NiMH sub-C battery, rechargeable up to 1000 times

Charging: 10 hour charger-holders, available with AC or 12V DC charge cords

Features

- IPX4 water-resistant
- 1 meter impact resistance tested
- Serialized for positive identification

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
SL-20XP-LED Type C (230V) AC/12V DC - Yellow	080926-25185-4	25185
SL-20XP-LED 240V AC/12V DC - Yellow	080926-25188-5	25188
SL-20XP-LED 120V AC/12V DC - Yellow	080926-25183-0	25183
SL-20XP-LED Type A (100V) AC/12V DC - Yellow	080926-25190-8	25190
SL-20XP-LED Type C (230V) AC/12V DC - Black	080926-25105-2	25105
SL-20XP-LED 240V AC/12V DC - Black	080926-25108-3	25108
SL-20XP-LED 120V AC/12V DC - Black	080926-25103-8	25103
SL-20XP-LED Type A (100V) AC/12V DC - Black	080926-25110-6	25110
SL-20XP-LED Type C (230V) AC/12V DC - Orange	080926-25125-0	25125
SL-20XP-LED 240V AC/12V DC - Orange	080926-25128-1	25128
SL-20XP-LED 120V AC/12V DC - Orange	080926-25123-6	25123
SL-20XP-LED Type A (100V) AC/12V DC - Orange	080926-25130-4	25130
SL-20XP-LED without Charger- Yellow	080926-25180-9	25180
SL-20XP-LED without Charger - Black	080926-25100-7	25100
SL-20XP-LED without Charger - Orange	080926-25120-5	25120

Item	UPC	Part #
SL-20XP-LED Type C (230V) AC - Yellow	080926-25184-7	25184
SL-20XP-LED 240V AC - Yellow	080926-25186-1	25186
SL-20XP-LED 120V AC - Yellow	080926-25181-6	25181
SL-20XP-LED Type A (100V) AC - Yellow	080926-25189-2	25189
SL-20XP-LED Type C (230V) AC - Black	080926-25104-5	25104
SL-20XP-LED 240V AC - Black	080926-25106-9	25106
SL-20XP-LED 120V AC - Black	080926-25101-4	25101
SL-20XP-LED Type A (100V) AC - Black	080926-25109-0	25109
SL-20XP-LED Type C (230V) AC - Orange	080926-25124-3	25124
SL-20XP-LED 240V AC - Orange	080926-25126-7	25126
SL-20XP-LED 120V AC - Orange	080926-25121-2	25121
SL-20XP-LED Type A (100V) AC - Orange	080926-25129-8	25129
SL-20XP-LED 12V DC - Yellow	080926-25182-3	25182
SL-20XP-LED 12V DC - Black	080926-25102-1	25102
SL-20XP-LED 12V DC - Orange	080926-25122-9	25122

See reverse for additional part numbers





Item	UPC	Part #
Charge Sleeve Assembly (Cord not included)	080926-22052-2	22052
DC2 direct wire charge cord	080926-22050-8	22050
DC1 Charge Cord	080926-22051-5	22051
120V AC charge cord	080926-22311-0	22311
Type A (100V/120V) AC charge cord	080926-22060-7	22060
Type C (230V) AC charge cord	080926-22061-4	22061
240V AC charge cord	080926-22241-0	22241
5 Unit Bank Charger, 120V	080926-21400-2	21400
5 Unit Bank Charger DC	080926-21401-9	21401
Battery Stick (NiCd)	080926-77175-8	77175
Battery Stick (NiMH)	080926-77375-2	77375
Lamp Module	080926-25127-4	25127
SL-20X-LED/SL-20XP-LED Switch Module*	080926-25141-0	25141
Lens (Clear polycarbonate)*	080926-20160-6	20160
Safety Wand Red	080926-22511-4	22511
Safety Wand Blue	080926-22512-1	22512
Safety Wand Glow in the Dark	080926-22513-8	22513
Safety Wand White	080926-22517-6	22517
Safety Wand Yellow	080926-22519-0	22519
Ring Holder	080926-22911-2	22911
Holster, SL Series (Nylon)	080926-25090-1	25090

*not pictured

