

## Stripping machine - WF 1000 120V - 1212258

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Stripping machine with integrated graphic display, for conductors and cables up to 6 mm in diameter, 120 V version

### Why buy this product

- ✓ The clamping force automatically adjusts itself to the required extraction force
- ✓ Compact stripping machine for automatically stripping conductors with a cross section of 0.08 to 6 mm<sup>2</sup>
- ✓ Pressure points on sensitive insulation are avoided
- ✓ Even special types of insulation, such as PTFE and silicone, can be stripped in addition to standard types
- ✓ Multi-strand cables with a diameter of up to 6 mm can also be stripped
- ✓ The stripping dimensions are set individually via knobs and are shown on the large display
- ✓ Partial stripping is supported

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 457019
GTIN	4046356457019

### Technical data

#### Dimensions

Length (b)	363 mm
Width (a)	141 mm
Height (c)	221 mm
Diameter, conductor entry opening	6 mm

#### General

Compression	trapezoidal
Power consumption	160 VA
Maximum throughput	6
Min. cross section	0.08 mm <sup>2</sup>

# Stripping machine - WF 1000 120V - 1212258

## Technical data

### General

Max. cross section	6 mm <sup>2</sup>
Minimum stripping length	2 mm
Maximum stripping length	20 mm
Partial stripping length range minimum	2 mm
Partial stripping length range maximum	20 mm
Weight	9.5 kg
Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 25;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01549
-----	---	--------------------------

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>