






FEMALE END VIEW	MALE END VIEW	TYPICAL PANEL CUTOUT	SPECIFICATIONS																													
 <p>1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK</p>	 <p>1 = BROWN 2 = WHITE 3 = BLUE 4 = BLACK</p>		<table border="1"> <tr><td>CONTACT CARRIER MATERIAL</td><td>TPU OR NYLON</td></tr> <tr><td>MOLDED HEAD MATERIAL/COLOR</td><td>TPU/YELLOW</td></tr> <tr><td>CONTACT MATERIAL/PLATING</td><td>BRASS/GOLD</td></tr> <tr><td>HOUSING, LOCKNUT MATERIAL/FINISH (J1)</td><td>316 STAINLESS STEEL/PASSIVATED</td></tr> <tr><td>COUPLING NUT MATERIAL/FINISH (P1)</td><td>STAINLESS STEEL/PASSIVATED</td></tr> <tr><td>O-RING MATERIAL</td><td>NITRILE</td></tr> <tr><td>RATED CURRENT [A]</td><td>4.0 A</td></tr> <tr><td>RATED VOLTAGE [V]</td><td>250 V</td></tr> <tr><td>OUTER CABLE JACKET MATERIAL/COLOR</td><td>PVC/YELLOW</td></tr> <tr><td>CONDUCTOR INSULATION MATERIAL</td><td>PVC</td></tr> <tr><td>NUMBER OF CONDUCTORS [AWG]</td><td>4x18 AWG</td></tr> <tr><td>TEMPERATURE RANGE</td><td>-40°C to +105°C (-40°F to +221°F)</td></tr> <tr><td>PROTECTION CLASS</td><td>MEETS NEMA 1,3,4,6P AND IEC IP68</td></tr> <tr><td>ACCOMODATES WALL THICKNESS (J1)</td><td>UP TO .118" (3.0mm)</td></tr> </table>	CONTACT CARRIER MATERIAL	TPU OR NYLON	MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW	CONTACT MATERIAL/PLATING	BRASS/GOLD	HOUSING, LOCKNUT MATERIAL/FINISH (J1)	316 STAINLESS STEEL/PASSIVATED	COUPLING NUT MATERIAL/FINISH (P1)	STAINLESS STEEL/PASSIVATED	O-RING MATERIAL	NITRILE	RATED CURRENT [A]	4.0 A	RATED VOLTAGE [V]	250 V	OUTER CABLE JACKET MATERIAL/COLOR	PVC/YELLOW	CONDUCTOR INSULATION MATERIAL	PVC	NUMBER OF CONDUCTORS [AWG]	4x18 AWG	TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)	PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68	ACCOMODATES WALL THICKNESS (J1)	UP TO .118" (3.0mm)	
CONTACT CARRIER MATERIAL	TPU OR NYLON																															
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW																															
CONTACT MATERIAL/PLATING	BRASS/GOLD																															
HOUSING, LOCKNUT MATERIAL/FINISH (J1)	316 STAINLESS STEEL/PASSIVATED																															
COUPLING NUT MATERIAL/FINISH (P1)	STAINLESS STEEL/PASSIVATED																															
O-RING MATERIAL	NITRILE																															
RATED CURRENT [A]	4.0 A																															
RATED VOLTAGE [V]	250 V																															
OUTER CABLE JACKET MATERIAL/COLOR	PVC/YELLOW																															
CONDUCTOR INSULATION MATERIAL	PVC																															
NUMBER OF CONDUCTORS [AWG]	4x18 AWG																															
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)																															
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68																															
ACCOMODATES WALL THICKNESS (J1)	UP TO .118" (3.0mm)																															



CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:
1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com
MATERIAL SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DRFT RDS DATE 03/02/10 APVD SCALE 1=1.0	DESCRIPTION FKFDV 4.4-*--RSCV 4.4T
FINISH SEE SPECIFICATIONS	CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT MILLIMETER [INCH] DO NOT SCALE THIS DRAWING	IDENTIFICATION NO. REV C FILE: 777025979 SHEET 1 OF 1

C	UPDATE CABLE DIAMETER	KMY	01/05/12	37156
REV	DESCRIPTION	BY	DATE	ECO NO.