

# 1092 Series 0.500" (12.7mm) LED Panel Mount Indicators



Available in four different lens styles, four diffused lens colors and operating voltage of 12V, 28V and 125VAC Snap fit designed for ease of assembly and tab terminals termination style















# **Application**

- Industrial
- Transportation
- Food Service

- People Mover
- Medical
- Maritime

- Oil and Gas Industry
- Manufacturing
- Automation & Control


## Key features

- · Four colors available: Red, Green, Amber and Blue
- Four different lens styles available: Hi Hat, Hi Dome, Semi Dome and Small Dome
- Snaps fit into 0.500" (12.7mm) panel hole
- Front panel snap-in mounting requires no additional hardware
- 0.187" (4.75) tab terminal
- 4.4"/4.8" wire leads version also available
- Available in wide operating voltage of 12V, 28V and 125VAC
- High brightness LEDs for daylight viewing
- Transparent and diffused lenses provide visibility during the daylight
- 'D' mounting hole aids anti-rotation
- Designed, manufactured and tested in accordance with the relevant UL and CSA standards
- Compliant with RoHS and REACH requirements
- Life expectancy of 100,000 hours
- Order speed nuts separately to provide maximum fastening power with minimal installation torque.
- Order gasket separately to provide water, oil, air and dust tight
- For customized options please contact us



# Ordering Data

The 1092 Series is available in a range of standard features and options. To specify your Panel Mount Indicator, simply choose one option from each column. An example is shown below



**Example:** 1092QD5-12V

1092 Tab Terminals with Semi-Dome lens - Green LED and 12 Volts



# Accessories Ordering Data [order separately]

Speed Nut: SN0461-C






O'Ring Gasket: SPC472







# **Product Dimensions**


#### Hi-Dome






#### Hi-Hat







## Semi Dome





#### Small Dome






# Mounting Hole (All)



Standard Mounting Hole



Dimensions in inches

# **Product Specifications**

Materials	
Housing	White Nylon UL94 V-2
Lens	Transparent Polycarbonate UL94 V-2
Bezel	Polished stainless steel
Tab terminals	Quick-connect tinned brass

Voltage Table		
Nominal	VAC	Nominal
12V	10 to 14	10 to 14
28V	26 to 30	26 to 30
125V	105 to 125	-

Temperature Specifications	
Operating	-40°C to +85°C
Temperature	-40°F to +185°F
Storage	-40°C to +85°C
Temperature	-40°F to +185°F

Installation Specifications	
Mounting Hole	0.500" to 0.505" (12.70 to 12.83 mm)
D-Mounting Hole	0.470" to 0.475" (11.94 to 12.07 mm)
Panel Thickness	0.020" to 0.100" (0.51 to 2.54 mm)
Tab Terminals	0.187" (4.75mm) terminals

Internal Resistor	
12V	390Ω
28V	1200Ω
125V	15000Ω + rectifier diode
Forward Current	054

Forward Current Rating	25mA

# Accessory options [order separately]


## **O-Ring Gasket**

Part Number: SPC472

The 1092 Gasket is designed to seal many types of media, including water, air, dust, and oil.

The panel gasket is intended to provide a seal between the panel and the 1092 Panel Mount Indicator.

Meets ASTM D2000 standard.



Dimensions in inches [mm]

Materia	
Buna-N, Durometer	A50, black

Installation Specification	
Internal Diameter	0.472" (12 mm)
28V	0.059" (1.5 mm)
Operational Temperature	-30°F to +225°F



## Accessory options [order separately]


#### Push-on speed nut

Part Number: SN0461-C

Description: Speed nut with coating, which secures the indicator in place

- One piece, self-locking, heat-treated, spring-steel fastener that replaces threaded nut, lock washer or spanner washer
- Eliminates time-consuming assembly operations
- Fast and easy to apply, the speed nut fastener provides maximum holding power at minimum cost per fastener
- It does not shake loose from vibration, yet can be easily loosened without worry about rust-frozen screw threads
- For smaller components where space is premium
- Requires less torque than standard hex-nuts
- Can be installed prior to painting process so threads won't fill.







Dimensions in inches [mm]

Material	
Speed Nut (one piece)	Spring Steel

Installation Specification	
Stud Size	0.485" (12.319mm)

# Compliances and Approvals









