speco technologies

NEXUS™ UL® Contractor Series 6.5" 70V Metal Back Can Speakers

(sold in pairs)



N E X U S

SP6NXCTUL

Speco Technologies' Nexus Contractor Speakers Commercial Line utilizes premium quality components to provide a network of sound and paging for even the most demanding commercial environments. The high-end NXC Series features heavy-duty, industrial metal back cans that provide component protection and safety while enhancing the speakers' full-range bass sound. Removable "Quick-Snap" connection terminals provide easy access and optimal angles for connecting speaker wire. A wattage selector dial simplifies transformer settings. Mounted security loops allow for a support cable run and ceiling support brackets are included. Most importantly, these speakers have met or exceeded the strict UL 1480 requirements for fire safety.

Features

- · Fire retardant metal back can
- Quick-snap terminal connections
- 70V transformer dial

- · Mounting brackets included
- · Metal safety loop for securing
- Ported bass

Specifications_

- 6.5" Polypropylene Woofer w/Rubber Surround
- ¾" Silk Dome Tweeter
- Frequency Response: 60Hz to 20kHz
- Sensitivity: 87db 1w/1m
- · Impedance: 8 Ohms

- Max power handling: 80W
- Transformer settings: 30W, 15W, 7.5W, 3.7W & 1.9W
- Dimensions: 10.25" Diameter x 7.75" Depth
- Cut Out Dimensions: 8.75"
- UL 1480 Rated

Specifications subject to change