


ALWAYS WIRE A LOAD IN SERIES WITH THE SENSOR.

WIRING DIAGRAM



0.2 METERS 0.2 METERS 2.36 [60.0] SBV 3T CONNECTOR
1/2-20UNF

SPECIFICATIONS	
RATED OPERATING DISTANCE	10mm [.394"]
MOUNTING MODE	NON-FLUSH
HYSTERESIS	3-15%
MIN. REPEAT ACCURACY	≤ 2%
TEMPERATURE DRIFT	≤±10%
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)
RATED OPERATIONAL VOLTAGE (AC/DC)	20-250 VAC/10-300 VDC
RATED OPERATIONAL CURRENT (AC/DC)	≤400 mA/≤300 mA
MAINS FREQUENCY	40-60 Hz
RESIDUAL CURRENT	≤ 1.7 mA
RATED INSULATION VOLTAGE	≤1.5 kV
SURGE CURRENT	≤8.0 A (≤10 ms MAX. 5 Hz)
MAX. VOLTAGE DROP	≤6 V
OUTPUT FUNCTION	2-WIRE, NORMALLY OPEN, AC/DC SELF-CONTAINED
SMALLEST OPERATING CURRET	≥ 3 mA
MAX. SWITCHING FREQUENCY	≤0.02 kHz
HOUSING MATERIAL	SST
SHOCK RESISTANCE	30 g, 11 ms
VIBRATION RESISTANCE	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)
DEGREE OF PROTECTION	IP67
SWITCHING STATUS INDICATION	LED, RED

SOURCE DRAWING - FOR REFERENCE ONLY

3RD ANGLE PROJECTION THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 turck inc 2. (763) 553-7300 DOCUMENT WITHOUT WRITTEN PERMISSION IS High Technology Sensors and Automation Controls 3. (763) 553-0708 fax PROHIBITED. turck.com DATE 08/06/12 MATERIAL DESCRIPTION RDS NI10-EG18-AZ3X-0.2M-SBV 3T/S1023 ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR SCALE A.F. 1 = 1.5SEE SPECS 1. "/S1023" DESIGNATES WET/WASHDOWN APPLICATIONS. LENSED LEDS AND SERPENTINE FULLY POTTED INTERNAL CABLE. UNIT OF MEASUREMENT REFERENCE ONLY IDENTIFICATION NO. REV FINISH INCH [MILLIMETER] CONTACT TURCK FOR MORE T4330587 DRAWING PROCESSED AS PART OF ECO 39587 KMY 08/07/12 39587 SEE SPECS INFORMATION DESCRIPTION DATE ECO NO. FILE: T4330587 SHEET 1 OF 1 BY DO NOT SCALE THIS DRAWING

RELATED DOCUMENTS