

ENGLISH

Datasheet

Blue 30m Nylon Air Hose, $-40 \rightarrow +80^{\circ}$ C, Application Various

RS Stock number 723-933

INDUSTRIAL NYLON TUBING The Extra Flexible Nylon

Special Features

- Resistant to a wide range of chemicals (see Chemicals Resistance Table)
- Silicone free
- Abrasion resistance excellent
- Mirror smooth inner for improved flow







STOCK SIZES - IMPERIAL

Siz	e	Min. Bend	Burst Pressure						
I.D.	Q.D.	Radius	PSI	BAR					
FLEXIBLE MEDIUM GAUGE									
.117	3/16	3/4	650	44					
.170	1/4	1	650	44					
.212	5/16	1 1/2	650	44					
.265	3/8	2	650	44					
.250	3/8	2 1/2	650	44					
.375	1/2	3	650	44					
	I.D. DIUM GAUGI .117 .170 .212 .265 .250	DIUM GAUGE .117 3/16 .170 1/4 .212 5/16 .265 3/8 .250 3/8	Size Bend Radius I.D. 0.D. Radius DIUM GAUGE	Size Bend Radius Pres I.D. O.D. Radius PSI DIUM GAUGE .117 3/16 3/4 650 .117 3/16 3/4 650 .122 5/16 1 1/2 650 .265 3/8 2 650 .250 3/8 2 1/2 650					

STOCK SIZES - METRIC

Product	Siz	te		Nominal Wall Thickness	Pres	Burst ssure 20°C	Bend Radius
Ret	00.	Tol.	I.D.	mm	P.S.I.	BAR	m
FLEXIBLE MEDIUM GAUGE							
		+0.05/					
NMSF04M	4	-0.07	2.5	0.75 ± 0.08	917	62	25mm
		+0.05/					
NMSF05M	5	-0.07	3.3	0.85 ± 0.08	850	58	30mm
		+0.05/					
NMSF06M	6	-0.10	4	1.00 ± 0.08	840	57	35mm
		+0.05/					
NMSF08M	8	-0.10	5.5	1.25 ± 0.08	802	55	45mm
		+0.05/					
NMSF10M	10	-0.10	7	1.50 ± 0.08	773	53	60mm
		+0.05/					
NMSF12M	12	-0.10	8.5	1.75 ± 0.08	755	51	70mm

ENGLISH

PHYSICAL PROPERTIES	METHOD	UNIT	
Melting Point Range	Polarisation Microscope	°C	162 - 170
Density	DIN 53479	9/cm3	1.05
Water Absorption	Condition at 65% RH & 20°C	%	1.4
Water Saturation	Condition at 65% RH & 20°C	Kp/cm2	160
Tensile Strength, yield	DIN 53455	Kp/cm2	280
Elongation at yield	DIN 53455	%	350
Tensile Strength at break	DIN 53455		
Elongation at break	DIN 53455	Kp/cm2	140
Flexural Strength at conventional deflection	DIN 53452	Kp/cm2 cmkp/cm2	210 No break
Ball Indentation hardness	VDE 0303 . 60 sec		51
Impact Strength	DIN 53453		
Charally the transport D			

Shore Hardness - Scale D

Max. Temperatures for long term usage in: AIR, WATER & OIL 80°C

Max. Temperatures for short term: 100°C

NOTE: Working pressures - allow a factor of between 2 - 1 and 4 - 1 subject to operating conditions.